



## TECHNICAL DATA

Steel lug lock cable tie

Temperature range -60°C to +105°C

### ■ STRUCTURE

- Material: Polyamide (PA) 6.6
- Flammability acc. to UL 94 (V2)

- halogen-free
- silicone-free

### ■ APPLICATION

- Smooth, notchless cable tie with steel lug lock made of corrosion-resistant, non-magnetic steel and rounded edges. This technology enables the cable tie to offer excellent binding properties even under most rigorous conditions such as heat, cold, humidity etc. It is resistant to vibrations and external influences.

### ■ PROPERTIES

Type	Length mm	Width mm	Bundle Ø mm	Capacity N	Packaging unit (in pc.)	black Part no.
TY23MX-RW	92.0	2.4	1.5 - 22	80	1000	<b>11007539</b>
TY232MK-RW	203.0	2.5	1.5 - 51	80	1000	<b>11007540</b>
TY234MX-RW	356.0	2.4	1.5 - 102	80	1000	<b>11007541</b>
TY24MX-RW	140.0	3.6	2 - 35	180	1000	<b>11007542</b>
TY242MX-RW	208.0	3.6	2 - 51	180	1000	<b>11007543</b>
TY26MX-RW	248.0	3.6	2 - 76	130	1000	<b>11007544</b>
TY244MX-RW	368.0	3.6	2 - 102	130	1000	<b>11007545</b>
TY25MX-RW	186.0	4.8	3 - 48	220	1000	<b>11007546</b>
TY253MX-RW	290.0	4.8	3 - 78	220	1000	<b>11007547</b>
TY28MX-RW	360.0	4.8	3 - 102	220	1000	<b>11007548</b>
TY271MX-RW	150.0	7.6	6 - 31	540	500	<b>11007549</b>
TY272MX-RW	222.0	6.9	6 - 51	540	500	<b>11007550</b>
TY27MX-RW	340.0	6.9	6 - 102	540	500	<b>11007552</b>
TY277MX-RW	617.0	6.9	6 - 177	540	500	<b>11007551</b>
TY29MX-RW	771.0	6.9	6 - 229	540	500	<b>11007553</b>