


HELUPOWER® CU-STRAP FLAT BRAIDED BARE



TECHNICAL DATA

Cu Earthing Strap

Temperature range -20°C to +125°C
wire diameter 0.2 mm

■ STRUCTURE

- Material: copper blank

■ PROPERTIES

- rounded contacts
- contact areas made of seamless, pressed ferrules
- suited for applications with repeated bending

■ APPLICATION

- automobile industry
- Railway Industry and Rail Vehicles
- robots
- Control cabinet construction
- energy sector
- control panel elements
- for earthing purposes
- for EMC applications (interference elimination)

■ NOTES

- Legend:
 Dimensions
 B1 - Stud hole
 B2 - Stud hole
 L - Length

Part no.	Cross-sec. mm ²	Length L mm	Boring M1 / M2 mm
11026932	10	200.0	5.5 / 5.5
11026937	10	400.0	5.5 / 5.5
11026933	10	200.0	6.5 / 6.5
11026935	10	300.0	6.5 / 6.5
11026938	10	400.0	6.5 / 6.5
11026940	10	500.0	6.5 / 6.5
11026942	10	700.0	6.5 / 6.5
11026934	10	200.0	8.5 / 8.5
11026936	10	300.0	8.5 / 8.5
11026939	10	400.0	8.5 / 8.5
11026941	10	500.0	8.5 / 8.5
11026943	16	200.0	6.5 / 6.5
11026945	16	300.0	6.5 / 6.5
11026947	16	400.0	6.5 / 6.5
11026949	16	500.0	6.5 / 6.5
11026944	16	200.0	8.5 / 8.5
11026946	16	300.0	8.5 / 8.5
11026948	16	400.0	8.5 / 8.5
11026950	16	500.0	8.5 / 8.5
11026951	16	600.0	8.5 / 8.5

Part no.	Cross-sec. mm ²	Length L mm	Boring M1 / M2 mm
11026955	25	400.0	6.5 / 6.5
11026952	25	200.0	8.5 / 8.5
11026953	25	250.0	8.5 / 8.5
11026954	25	300.0	8.5 / 8.5
11026956	25	500.0	8.5 / 8.5
11026960	35	1200.0	8.5 / 8.5
11026957	35	350.0	8.5 / 8.5
11026958	35	400.0	8.5 / 8.5
11026959	35	500.0	8.5 / 8.5
11026961	50	150.0	6.5 / 6.5
11026962	50	150.0	8.5 / 8.5
11026964	50	400.0	8.5 / 8.5
11026963	50	300.0	10.5 / 10.5
11026965	70	1500.0	10.5 / 10.5
11026966	70	300.0	10.5 / 10.5
11026967	70	450.0	10.5 / 10.5
11026968	70	600.0	10.5 / 10.5
11026981	70	800.0	10.5 / 10.5
11026982	120	120.0	10.5 / 10.5