



TECHNICAL DATA

Stainless steel cable gland

Temperature range	-20°C to +100°C short term -40°C to +150°C
Protection class	IP 68 - 5 bar, 30 min.

- smooth surface prevents to adhere harmful microorganisms and allows for easy cleaning
- internal thread prevents dirt accumulation
- suitable for high pressure steam cleaning
- resistant against chemical cleaning supplies
- high corrosion resistance
- ECOLAB certified

■ STRUCTURE

- Material: Stainless steel 1.4305 / AISI 303
- Seal: thermoplastic elastomers (TPE)

■ APPLICATION

- Food and beverage industry
- Pharmaindustrie
- Reinraumtechnologie
- Biotechnologie
- chemical industry

■ PROPERTIES

- optimal strain relief through strain relief element
- easy to assemble, time and cost savings
- watertight, dust-tight
- protection against ingress of water and foreign material into enclosure

■ NOTES

- For tightening from outside use the listed tightening tool
Assembly with commercial socket wrench
Delivery including counternut
- Legend:
Dimensions
TD - Thread Diameter
TL - Thread Length
SZ - Spanner Size

metric thread

Part no.	Size	Cable Ø from / to mm	Thread length mm	Spanner size mm	Packaging unit (in pc.)
11021383	M12 x 1.5	3.0 - 6.5	6.0	14	50
11021384	M16 x 1.5	5.0 - 10.0	7.0	18	50
11021385	M20 x 1.5	6.0 - 12.0	8.0	22	50
11021386	M25 x 1.5	12.0 - 17.0	10.0	28	50