

HELUCHAIN® TOPSERV® 201-PVC UL/CSA

compatible with servo cables from well known manufacturers



HELUCHAIN® TOPSERV® 201-PVC 0,6/1 kV E170315 AWM DESINA CE

TECHNICAL DATA

PUVCMotor and servo cable acc. to UL Std. 758 (AWM) Style 21179

Temperature range	flexible 0°C to +90°C fixed -20°C to +90°C
Nominal voltage	VDE AC U0/U 600/1000 V UL (AWM) AC 1000 V
AC Test voltage	3000 V acc. to DIN VDE
Minimum bending radius	flexible 7.5 x outer Ø fixed 4 x outer Ø

CABLE STRUCTURE

- Copper wire bare, extra finely stranded acc. to DIN VDE 0295 Class 6 / IEC 60228 Class 6
- Core insulation: PP
- Core identification:
 - Power supply cores
 - Core 1: black with imprint U/L1/C/L+
 - Core 2: black with imprint V/L2
 - Core 3: black with imprint W/L3/D/L-
- Control cores
 - Pair 1: black-br1, white-br2
- G = with protective conductor GN-YE,
x = without protective conductor
- Screened cores: control cores in pairs, with tinned copper wires, approx. Coverage 95%
- Power supply cores laid up with optimal lay length and stabilising filler
- Ripcord
- Inner sheath: TPE, extruded filler
- Screen: braided screen of tinned copper wires, approx. Coverage 85%
- Polyester fleece wrapped
- Outer sheath: PVC
- Sheath colour: see table
- Length marking: in metres

PROPERTIES

- resistant to: oil
- low capacity
- suitable for drag chain application
- Drag chain parameters
 - Acceleration (max.): 10 m/s²
 - Velocity (max.), gliding: 5 m/s
 - Traverse path (max.): 100 m
- These cables are produced to high quality specifications are conform to the DESINA® standard
- The materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers

TESTS

- flame-retardant acc. to DIN VDE 0482-332-1-2 / DIN EN 60332-1-2 / IEC 60332-1-2, UL VW-1, CSA FT1
- certifications and approvals:
- ECOLAB®

APPLICATION

This PVC-drag chain cable is suitable for use in machinery, plant engineering, robotics, as well as automation, drive, control, and production technology. A key advantage lies in the TPE inner sheath, which is specially designed for long travel distances and high accelerations. In addition, a ripcord is integrated into the inner sheath, enabling faster and easier processing. Furthermore, the cable stands out due to its high abrasion resistance and oil resistance, ensuring reliable performance even under intensive mechanical stress. Thanks to the robust PVC sheath, it offers a long service life, reduces downtime, and helps increase system availability.

NOTES

- Brackets () mean screen
- DESINA is a registered trademark and stands for decentralized and standardized installation technology for machine tools and production systems.
- for use in energy supply systems:
- 1) the assembly instructions must be observed
- 2) for special applications, we recommend contacting us and using our data entry form for energy supply systems

Part no.	No. cores x cross-sec. mm ²	for system	Sheath colour	Outer-Ø approx. mm	Cu factor per km	Weight kg/km, approx
11029600	(4G1,5 + (2x1,5)D)C	Divers	orange	13.3	146.7	258.0
11028110	(4G2,5 + (2x1,5)D)C	Divers	orange	14.2	191.5	313.0
11028123	(4G4 + (2x1,5)D)C	Divers	orange	15.8	254.7	403.0
11028126	(4G6 + (2x1,5)D)C	Divers	orange	17.4	337.2	510.0