

HELUPOWER® ROBOFLEX®-D PUR UL/CSA

EMC-preferred type



TECHNICAL DATA

PUR robot cable acc. to UL-Std. 758 (AWM) Style 21209, CSA-Std. C22.2 No. 210 - AWM I/II A/B

| | |
|------------------------|-----------------------------------------------------------|
| Temperature range | flexible -30°C to +90°C fixed -40°C to +90°C |
| Nominal voltage | VDE AC U ₀ /U 600/1000 V UL (AWM) AC 1000 V |
| Test voltage core/core | 3000 V |
| Minimum bending radius | fixed 5x Outer-Ø flexible: see properties |

CABLE STRUCTURE

- Copper wire bare, extra finely stranded acc. to DIN VDE 0295 Class 6 / IEC 60228 Class 6
- Core insulation: PP
- Core identification acc. to DIN VDE 0293-334, black cores with consecutive labeling in white digits
- G = with protective conductor GN-YE
- Cores stranded with optimally matched lay lengths
- Fleece wrapping
- Screen: helically wound tinned copper wires, approx. coverage 90%
- Fleece wrapping
- Outer sheath: Special grade of full polyurethane acc. to DIN VDE 0207-363-10-2 / DIN EN 50363-10-2 (compound type TMPU)
- Sheath colour: see table
- Length marking: in metres

PROPERTIES

- resistant to: oil, UV radiation, ozone, oxygen, weathering effects, hydrolysis, microbes, coolants, hydraulic fluids, acids, alkalis, greases, seawater and wastewater
- highly abrasion-resistant, notch-resistant, tear-resistant, cut-resistant, wear-resistant, low adhesion
- smooth, high-quality core insulation for eased sliding and optimized core stranding ensure long service-life within applications that request combined bending and torsion movements
- for outdoor use

- torsion rated
- suitable for use in drag chains
- Torsion parameters
Acceleration (max.): 60 °/s²
Velocity (max.): 180 °/s
Minimum bending radius: 10x Outer-Ø
Torsional stress up to 180 °/m: 5 Mio. Cycles (max.)
- Drag chain parameters
Acceleration (max.): 10 m/s²
Velocity (max.), unsupported: 3 m/s
Velocity (max.), gliding: 2 m/s
Traverse path (max.): 10 m
Minimum bending radius (Traverse path ≤ 3m): 10x Outer-Ø
Minimum bending radius (Traverse path > 3m): 12.5x Outer-Ø
Bending cycles (max.): 5 Mio.
- halogen-free
- the materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers

TESTS

- halogen-free acc. to DIN VDE 0482-754-1 / DIN EN 60754-1 / IEC 60754-1
- flame-retardant acc. to DIN VDE 0482-332-1-2 / DIN EN 60332-1-2 / IEC 60332-1-2, UL VW-1, CSA FT1
- oil-resistant acc. to DIN VDE 0473-811-404 / DIN EN 60811-404 / IEC 60811-404
- UV-resistant acc. to DIN EN ISO 4892-2
- weather-resistant acc. to DIN EN ISO 4892-2

APPLICATION

Power supply cable designed for combined torsion and bending movements; for use in assembly and welding robots, in material handlings and automation centres, in transport and conveyor systems, on rotary and swivel tables and wherever a defined cable routing with only alternating bending movements is not applicable, but 3D-movements and torsional load have an impact on the cable; for applications with the highest requirements on mechanical, chemical and thermal resilience. EMC= Electromagnetic compatibility; to optimize the EMC features we recommend a large round contact of the D-screen on both ends.

NOTES

- the conductor is metrically (mm²) constructed, AWG numbers are approximated, and are for reference only
- for use in energy supply systems:
 - 1) the assembly instructions must be observed
 - 2) for special applications, we recommend contacting us and using our data entry form for energy supply systems

HELUPOWER® ROBOFLEX®-D PUR UL/CSA

EMC-preferred type



Sheath color: black (RAL 9005)

| Part no. | No. cores x cross-sec. mm ² | AWG, approx. | Outer Ø mm, approx. | Cu-weight kg/km | Weight kg/km, approx. |
|----------|----------------------------------------|--------------|---------------------|-----------------|-----------------------|
| 11022453 | 3 G 1.5 | 16 | 8.0 | 62.2 | 106.0 |
| 11022454 | 4 G 1.5 | 16 | 8.8 | 81.0 | 133.0 |
| 11022455 | 3 G 2.5 | 14 | 10.0 | 96.9 | 163.0 |
| 11022456 | 4 G 2.5 | 14 | 11.0 | 126.1 | 207.0 |
| 11022457 | 4 G 4 | 12 | 12.3 | 188.6 | 282.0 |
| 11022458 | 4 G 6 | 10 | 14.5 | 292.5 | 412.0 |

Sheath colour: grey (RAL 7001)

| Part no. | No. cores x cross-sec. mm ² | AWG, approx. | Outer Ø mm, approx. | Cu-weight kg/km | Weight kg/km, approx. |
|----------|----------------------------------------|--------------|---------------------|-----------------|-----------------------|
| 11022459 | 4 G 1.5 | 16 | 8.8 | 79.9 | 133.0 |
| 11022460 | 4 G 2.5 | 14 | 11.0 | 126.1 | 207.0 |
| 11022461 | 4 G 4 | 12 | 12.3 | 188.6 | 282.0 |
| 11022462 | 4 G 6 | 10 | 14.5 | 292.5 | 412.0 |