TOPFLEX®-MOTOR-EMV 103 low capacitance power

supply cable 1000 V, increased ampacity, meter marking





Technical data

- Special motor power supply cable for frequency converters acc. to UL-AWM style 21179
- Temperature range flexing -5°C to +70°C fixed installation -40°C to +80°C
- Permissible operating temperature at conductor +90°C
- Nominal voltage
 VDE U₀/U 600/1000 V
 UL 1000 V
- Test voltage 2500 V
- Insulation resistance min. 200 MOhm x km
- Coupling resistance acc. to different cross-sections max. 250 Ohm/km
- Mutual capacitance
 acc. to different cross-sections
 core/core 70 to 250 nF/km
 core/screen 110 to 410 nF/km
- Minimum bending radius fixed installation for outer Ø: up to 12 mm: 5x cable Ø > 12-20 mm: 7,5x cable Ø > 20 mm: 10x cable Ø free-movement for outer Ø: up to 12 mm: 10x cable Ø > 12-20 mm: 15x cable Ø

> 20 mm: 20x cable Ø

 Radiation-resistance up to 80x10⁶ cJ/kg (up to 80 Mrad)



Cable structure

- Bare copper, fine wire conductor to DIN VDE 0295 cl.5, BS 6360 cl.5 or IEC 60228 cl.5
- Core insulation of special-polymer
- Core identification to DIN VDE 0293-308
 up to 5 cores coloured
 - from 7 cores, black with continuous white numbering
- GN-YE conductor
- Cores stranded in concentric layers
- 1. Screen with special aluminium film
 2. Tinned copper braided screen,
 coverage approx. 80%
- Outer sheath of special PVC
- Sheath colour orange (RAL 2003)
- with meter marking

Properties

Tests

- PVC self-extinguishing and flame retardant acc. to DIN VDE 0482-332-1-2, DIN EN 60332-1-2, IEC 60332-1 (equivalent DIN VDE 0472 part 804 test method B)
- Features Special-Polymer-insulation secures a lower dielectric loss, double potential strength, high longevity and low screen-interference currents to include increased current carrying capacity
- Meets EMC requirements according to EN 55011 and DIN VDE 0875 part 11
- Low coupling resistance for high electromagnetic compatibility
- This screened motor supply cable with low mutual capacitance of the single cores because of the special Polymer core insulation and low screen capacitance enable a low-loss transmission of the power compared to PVC-sheathed connecting cables
- Due to the optimal screening an interference-free operation of frequency converters is obtained
- Design acc. to the requirements of VdS 3501:2006-04
- The materials used in manufacture are cadmium-free and contain no silicone and free from substances harmful to the wetting properties of lacquers

Note

 AWG sizes are approximate equivalent values. The actual cross-section is in mm².

Outer Ø Cop. Weight AWG-No.

Application

This UL/CSA motor power supply cable for the frequency converters assures electromagnetic compatibillity in plants and buildings, facilities with units and operating equipment where the fields of electromagnetic interference might cause adverse effects on the surroundings. As a supply and connecting cable for medium mechanical stresses in fixed installations and forced movements in dry, moist and wet environments. Used in the automotive and food industries, environmental technology, packaging industry, machine tools. Handling equipment, for SIMOVERT drives, they are particularly suitable for use with industrial pumps, ventilators, conveyor belts and air-conditioning installations and similar applications. Installation in hazardous areas. **EMC** = Electromagnetic compatibility

The screen must be connected at both ends and ensure large-area contact over the entire cable circumference for compliance with the functional interference requirements of EN 55011.

Part no. No.cores x

C €= The product is conformed with the EC Low-Voltage Directive 2006/95/EC.

Part no.	No.cores x cross-sec. mm ²	Outer Ø app. mm	Cop. weight kg/km	Weight app. kg/km	AWG-No.
22689	3 G 1,5	9,4	72,0	200,0	16
22690	4 G 1,5	10,4	95,0	230,0	16
22691	5 G 1,5	11,2	117,0	258,0	16
22692	7 G 1,5	13,2	148,0	281,0	16
22693	3 G 2,5	11,2	137,0	270,0	14
22694	4 G 2,5	12,5	150,0	300,0	14
22695	5 G 2,5	13,5	200,0	352,0	14
22696	7 G 2,5	16,0	230,0	473,0	14
22697	4 G 4	14.7	235.0	485 N	12

		cross-sec. mm²	app. mm	weight kg/km	app. kg/km	
22	698	5 G 4	15,4	321,0	567,0	12
22	699	7 G 4	18,2	352,0	603,0	12
22	700	4 G 6	15,2	320,0	633,0	10
22	701	5 G 6	16,8	439,0	679,0	10
22	702	7 G 6	20,0	501,0	771,0	10
22	703	4 G 10	19,5	533,0	860,0	8
22	704	5 G 10	21,6	711,0	1029,0	8
22	705	4 G 16	23,1	789,0	1290,0	6
22	706	4 G 25	27.1	1236.0	1862.0	4

Dimensions and specifications may be changed without prior notice. (RN07)



