


N2XS(F)2Y

6/10 kV, 12/20 kV, 18/30 kV, Copper conductor, XLPE insulated, PE sheath, longitudinally water-proof



TECHNICAL DATA

Medium voltage cable acc. to DIN VDE 0276-620, HD 620 S2, IEC 60502

Temperature range	during installation -20°C
Permissible operating temperature of the conductor	+90°C
Short circuit temperature at the conductor	+250°C (Short circuit temperature max. 5 s)
Nominal voltage	see table
Operating voltage	see table
Test voltage	see table
Minimum bending radius	15x Outer-Ø

CABLE STRUCTURE

- Copper conductor bare, stranded acc. to DIN VDE 0295 Class 2 / IEC 60228 Class 2
- Inner conductive layer
- Core insulation: XLPE acc. to HD 620 S2 (compound type DIX8)
- Outer conductive layer
- Longitudinally waterproof, conductive wrapping
- Screen: braiding of copper wires with one or two counter helix conductors
- Longitudinally waterproof wrapping
- Outer sheath: PE acc. to HD 620 S2 (compound type DMP2)
- Sheath colour: black

PROPERTIES

- for outdoor use
- direct burial
- the materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers

APPLICATION

Suitable for indoor installation and in cable ducts, outdoors, underground and in water as well as for installation on cable trays for industries, switch-boards and power stations. The PE-outer sheath is resistant to high mechanical stress for laying the cables. The inner conducting layer between the conductor and the XLPE insulation and the firmly bonded outer conducting layer on the XLPE insulation assures a construction free of partial discharges with high operational reliability.

NOTES

- rm = round, stranded conductor
- the conductor is metrically (mm²) constructed, AWG numbers are approximated, and are for reference only
- the PE outer sheath is not flame retardant acc. to DIN EN 60332-1-2
- for maximum operational reliability, the core insulation and the outer conductive layer are simultaneously extruded and permanently welded together. For installation, a peeling tool is recommended.

6/10 kV

Part no.	No. cores x cross-sec. mm ²	AWG, approx.	Operating voltage ¹⁾ max. kV	Test voltage kV	Outer Ø mm, approx.	Cu-weight kg/km	Weight kg/km, approx.
32560	1 x 35 rm / 16	2	12	21	26.0	518.0	1050.0
32561	1 x 50 rm / 16	1	12	21	28.0	662.0	1150.0
32562	1 x 70 rm / 16	2/0	12	21	30.0	854.0	1460.0
32563	1 x 95 rm / 16	3/0	12	21	31.0	1094.0	1700.0
32564	1 x 120 rm / 16	4/0	12	21	32.0	1334.0	2030.0
32565	1 x 150 rm / 25	300 kcmil	12	21	34.0	1723.0	2350.0
32566	1 x 185 rm / 25	350 kcmil	12	21	36.0	2059.0	2700.0
32567	1 x 240 rm / 25	500 kcmil	12	21	38.0	2587.0	3300.0
32568	1 x 300 rm / 25	600 kcmil	12	21	40.0	3163.0	3900.0
32569	1 x 400 rm / 35	750 kcmil	12	21	44.0	4234.0	4850.0
32570	1 x 500 rm / 35	1000 kcmil	12	21	47.0	5194.0	6000.0
79954	1 x 630 rm / 35	1250 kcmil	12	21	49.0	6442.0	7020.0

12/20 kV

Part no.	No. cores x cross-sec. mm ²	AWG, approx.	Operating voltage ¹⁾ max. kV	Test voltage kV	Outer Ø mm, approx.	Cu-weight kg/km	Weight kg/km, approx.
32571	1 x 35 rm / 16	2	24	42	31.0	518.0	1210.0
32572	1 x 50 rm / 16	1	24	42	33.0	662.0	1400.0
32573	1 x 70 rm / 16	2/0	24	42	34.0	854.0	1550.0

Continued on next page

N2XS(F)2Y



6/10 kV, 12/20 kV, 18/30 kV, Copper conductor, XLPE insulated, PE sheath, longitudinally water-proof

12/20 kV

Part no.	No. cores x cross-sec. mm ²	AWG, approx.	Operating voltage ¹⁾ max. kV	Test voltage kV	Outer Ø mm, approx.	Cu-weight kg/km	Weight kg/km, approx.
32574	1 x 95 rm / 16	3/0	24	42	36.0	1094.0	1800.0
32575	1 x 120 rm / 16	4/0	24	42	37.0	1334.0	2150.0
32576	1 x 150 rm / 25	300 kcmil	24	42	39.0	1723.0	2400.0
32577	1 x 185 rm / 25	350 kcmil	24	42	41.0	2059.0	2850.0
32578	1 x 240 rm / 25	500 kcmil	24	42	43.0	2587.0	3250.0
32579	1 x 300 rm / 25	600 kcmil	24	42	45.0	3163.0	3850.0
32580	1 x 400 rm / 35	750 kcmil	24	42	48.0	4234.0	4900.0
32581	1 x 500 rm / 35	1000 kcmil	24	42	52.0	5194.0	6100.0
33092	1 x 630 rm / 35	1250 kcmil	24	42	54.0	6442.0	7340.0

18/30 kV

Part no.	No. cores x cross-sec. mm ²	AWG, approx.	Operating voltage ¹⁾ max. kV	Test voltage kV	Outer Ø mm, approx.	Cu-weight kg/km	Weight kg/km, approx.
32582	1 x 50 rm / 16	1	36	63	37.0	662.0	1700.0
32583	1 x 70 rm / 16	2/0	36	63	38.0	854.0	1950.0
32584	1 x 95 rm / 16	3/0	36	63	40.0	1094.0	2300.0
32585	1 x 120 rm / 16	4/0	36	63	42.0	1334.0	2600.0
32586	1 x 150 rm / 25	300 kcmil	36	63	43.0	1723.0	3000.0
32587	1 x 185 rm / 25	350 kcmil	36	63	45.0	2059.0	3350.0
32588	1 x 240 rm / 25	500 kcmil	36	63	47.0	2587.0	4100.0
32589	1 x 300 rm / 25	600 kcmil	36	63	50.0	3163.0	4800.0
32590	1 x 400 rm / 35	750 kcmil	36	63	53.0	4234.0	5750.0
32591	1 x 500 rm / 35	1000 kcmil	36	63	56.0	5194.0	6700.0
708487	1 x 630 rm / 35	1250 kcmil	36	63	59.0	6442.0	7760.0

1) max. permissible operating voltage three-phase alternating current (AC) conductor/conductor