



HELUSOUND® 400 PVC

Speaker cables, round

HELUSOUND®



Type

Cable structure

Conductor material:
Core insulation:
Core colours:
Sheath material:
Cable external diameter:
Sheath colour:

Speaker cable HELUSOUND® 400 2x1,5

Copper, bare
PVC
rd, bk
PVC
approx. 6,6 mm
black

Electrical data

Conductor resistance, max.: 12,7 Ohm/km

Technical data

Weight: approx. 73,4 kg/km
Min. bending radius for laying: 33 mm
Operating temperature range min.: -10°C
Operating temperature range max.: +70°C
Copper weight: 28,8 kg/km

| Part no. | Cable structure | Conductor resistance Ohm / km | Outer diameter approx. mm | Cop. weight kg / km | Weight approx. kg / km |
|----------|-----------------|-------------------------------|---------------------------|---------------------|------------------------|
| 400089 | 2x1,5 | < 12,7 | 6,6 | 28,8 | 73,4 |
| 400090 | 2x2,5 | < 7,9 | 7,5 | 48,0 | 106,9 |
| 400091 | 2x4,0 | < 4,9 | 9,4 | 76,8 | 163,7 |
| 400092 | 4x2,5 | < 7,9 | 8,8 | 96,0 | 169,3 |
| 400093 | 4x4,0 | < 4,9 | 11,6 | 153,6 | 272,4 |
| 400060 | 8x2,5 | < 7,9 | 13,5 | 192,0 | 349,0 |
| 400094 | 8x4,0 | < 4,9 | 16,8 | 307,2 | 541,6 |

Dimensions and specifications may be changed without prior notice.

Application

All products of the HELUSOUND® 400 LOUDSPEAKER series impress with their extremely high flexibility. 0,15 stranded wires and a very soft PVC outer sheath make this possible. These cables are particularly used in mobile applications on stages, in studios or in the conference industry.