

Splice-Boxes partly equipped, Telescope



## Type

**19" splice boxes, telescope partially configured with couplings MM**

## Cage

Housing material:  
Cover lock:  
Colour:

Steel sheet  
Fastening by means of screws  
Grey similar to RAL 7035

## Equipment

Partially-configured  
Couplers

## Dimensions

Number of height modules (HM):  
Fastening dimensions:  
Width:

1  
19"  
225 mm

## Preferred types

Part no.	Number of couplers	Type of coupler	Unit
<b>801171</b>	4	ST	1
<b>801172</b>	8	ST	1
<b>801173</b>	12	ST	1
<b>801174</b>	24	ST	1
<b>801168</b>	2	SC duplex	1
<b>801169</b>	4	SC duplex	1
<b>801170</b>	6	SC duplex	1
<b>80996</b>	12	SC duplex	1
<b>803157</b>	2	LCdx	1
<b>803158</b>	4	LCdx	1
<b>803159</b>	6	LCdx	1
<b>803160</b>	12	LCdx	1

Dimensions and specifications may be changed without prior notice.

## Options

On request, different assembly variations, such as F-SMA, FC/PC, and DIN and/or diagonal cross section designs, are also available.

## Application

Glass fibre splice boxes are used as cable end enclosures for multi-core fibreoptic cables in 19" cabinets. The splice boxes described here are particularly suitable as a connecting unit for our pre-fabricated fibre-optic grooved cables.