
BUS Cables

CAN Bus fixed installed





Type Cable structure

Inner conductor Ø:

Core insulation:
Core colours:
Stranding element:
Separator:
Shielding 1:
Total shielding:
Outer sheath material:
Cable external diameter:
Outer sheath colour:

Electrical data

Characteristic impedance: Conductor resistance, max.: Insulation resistance, min.: Loop resistance: Mutual capacitance: Nominal voltage: Test voltage:

Technical data

Weight: bending radius, repeated: Operating temperature range min.: Operating temperature range max.: Caloric load, approx. value: Copper weight:

Norms

Applicable standards:

UL Style: CSA standard:



Fixed installation, indoor 2x2x0.34 mm² (stranded)

Copper, bare (AWG 22/7)
Foam-skin-PE
wh/bn, gn/ye
Double core
Polyester foil over stranded bundle
Cu braid, tinned
PVC

app. 8,5 mm \pm 0,3 mm Violet similar to RAL 4001

120 Ohm ± 10 % 55,4 Ohm/km 5 GOhm x km 110,8 Ohm/km max. 40 nF/km nom. 250 V 1,5 kV

app. 85 kg/km 130 mm -40°C +70°C 1,32 MJ/m 46,00 kg/km

CAN Bus acc. to ISO 11898-2 Flame-retardant acc. to IEC 60332-1-2 CMX 75°C (shielded) CSA FT1

Application

HELUKABEL® CAN Bus fixed installations and occasionally motion, for normal requirements. The two signal pairs are provided in the form twisted pairs. As a result, the diameter is somewhat larger than that of 801573. In the event of diameter problems, please have a look at this type. For cable lengths up to max. 40m (observe CAN specifications).

Part no. 803344, CAN BUS

Dimensions and specifications may be changed without prior notice.