


# BUS Cables

## Profibus L2 indoor



PVC



### Type

#### Cable structure

Inner conductor diameter:  
Core insulation:  
Core colours:  
Stranding element:  
Separator:  
Shielding 1:  
Total shielding:  
Outer sheath material:  
Cable external diameter:  
Outer sheath colour:

#### Fixed installation, indoor 1x2x0.64 mm

Copper, bare (AWG 22/1)  
Foam-skin-PE  
rd, gn  
2 cores + 2 fillers stranded together  
Polyester foil over stranded bundle  
Al-Foil  
Cu braid, tinned  
PVC  
app. 7,8 mm ± 0,2 mm  
Grey similar to RAL 7001

#### Fixed installation, indoor 1x2x0.64 mm

Copper, bare (AWG 22/1)  
Foam-skin-PE  
rd, gn  
2 cores + 2 fillers stranded together  
Polyester foil over stranded bundle  
Al-Foil  
Cu braid, tinned  
PVC  
app. 7,8 mm ± 0,2 mm  
Violet similar to RAL 4001

### Electrical data

Characteristic impedance:  
Conductor resistance, max.:  
Insulation resistance, min.:  
Loop resistance:  
Mutual capacitance:  
Test voltage:  
Attenuation:

150 Ohm ± 10 %  
55 Ohm/km  
5 GOhm x km  
110 Ohm/km max.  
30 nF/km nom.  
1,5 kV  
9,6 kHz < 2,5 dB/km  
38,4 kHz < 4,0 dB/km  
4 MHz < 22,0 dB/km  
16 MHz < 42,0 dB/km

150 Ohm ± 10 %  
55 Ohm/km  
5 GOhm x km  
110 Ohm/km max.  
30 nF/km nom.  
1,5 kV  
9,6 kHz < 2,5 dB/km  
38,4 kHz < 4,0 dB/km  
4 MHz < 22,0 dB/km  
16 MHz < 42,0 dB/km

### Technical data

Weight:  
bending radius, repeated:  
Operating temperature range min.:  
Operating temperature range max.:  
Caloric load, approx. value:  
Copper weight:

app. 69 kg/km  
120 mm  
-40°C  
+70°C  
0,99 MJ/m  
24,00 kg/km

app. 69 kg/km  
120 mm  
-40°C  
+70°C  
0,99 MJ/m  
24,00 kg/km

### Norms

Applicable standards:

UL Style:  
CSA standard:

Profibus acc. to DIN 19245 T3 and EN50170  
Flame-retardant acc. to IEC 60332-1-2  
CMX 75°C (shielded)  
CSA FT1

Profibus acc. to DIN 19245 T3 and EN50170  
Flame-retardant acc. to IEC 60332-1-2  
CMX 75°C (shielded)  
CSA FT1

### Application

HELUKABEL® Profibus L2 Indoor is designed for fixed indoor installation in Profibus industrial networks. Depending on the application, the colour grey (special colour) or violet (standard colour) is available. Otherwise, the technical characteristics of the two products are identical.

### Part no.

**80384**, Profibus L2

**81448**, Profibus L2

Dimensions and specifications may be changed without prior notice.