

Fibre Optic Breakout Cable robust, flexible

HCS

HELUCOM®
I-V(ZN)Y11Y



Cable structure

Core type: Composite buffered
Strain relief elements: Aramide
Outer sheath material: PUR
Outer sheath colour: Red

Temperature range

Laying, min.: -5°C
Laying, max.: +50°C
Operating, min.: -20°C
Operating, max.: +70°C

Other data

Oil-resistant

Designation	Number of fibres	Fibre type	Fibre category	Number of fibres per core	Outer Ø app. mm	Max. tensile force N	Min. stat. bending radius mm	Max. transverse pressure N / cm	Caloric load app. MJ / m	Weight kg / km	Part no.
I-V(ZN)Y11Y	2	HCS 200/230	Other	1	7,0	800	50,0	150	1,014	43,0	800980

Dimensions and specifications may be changed without prior notice.

Application

This HELUCOM® HCS fibre cable is suitable for fixed installation. Possible applications are normal and heavy-duty mechanical requirements for example in industrial environments. With the tight buffer construction, direct plug manufacturing, even on site, poses no problems. With a HCS fibre transmission lengths of up to 300m can be achieved.