


BUS Cables

I-BUS fixed installed



HELUKABEL®

PVC



Type Cable structure

Inner conductor diameter:
Inner conductor diameter 2:
Core insulation:
Core insulation 2:
Core colours:
Core colours 2:
Stranding element:
Separator:
Shielding 1:
Total shielding:
Outer sheath material:
Cable external diameter:
Outer sheath colour:

Electrical data

Characteristic impedance:
Conductor resistance, max.:
Insulation resistance, min.:
Loop resistance:
Mutual capacitance:
Test voltage:
Attenuation:

Technical data

Weight:
bending radius, repeated:
Operating temperature range min.:
Operating temperature range max.:
Caloric load, approx. value:
Copper weight:

Norms

Applicable standards:

UL Style:
CSA standard:

Application

HELUKABEL® I-Bus is designed for fixed installation and occasional motion, for normal Interbus installation and as a hybrid cable with integrated power supply.

Part no.

Dimensions and specifications may be changed without prior notice.

Fixed installation, indoor 3x2x0.22 mm²

Copper, bare (AWG 24/7)
-
PE
-
wh/bn, gn/rd, ye/gn
-
Double core
Polyester foil over stranded bundle
-
Cu braid, tinned
PVC
app. 7,0 mm ± 0,3 mm
Pastel turquoise similar to RAL 6034

100 Ohm ± 15 Ohm
87 Ohm/km
5 GOhm x km
175 Ohm/km max.
60 nF/km nom.
2 kV
256 kHz < 15,0 dB/km
772 kHz < 24,0 dB/km
1 MHz < 27,0 dB/km
4 MHz < 52,0 dB/km
10 MHz < 84,0 dB/km
16 MHz < 112,0 dB/km
20 MHz < 119,0 dB/km

app. 60 kg/km
60 mm
-40°C
+80°C
0,82 MJ/m
35,00 kg/km

interbus specification 2.0, IEC61158
Flame-retardant acc. to IEC 60332-1-2
AWM 2464 (80°C 300V)
CSA FT1

80778, I-BUS

Fixed installation, indoor 3x2x0.22 mm² + 3x1.0 mm²

Copper, bare (AWG 24/7)
Copper, bare (AWG 17/56)
PE
PE
wh/bn, gn/rd, ye/gn
bu, rd, gnye
Double core
Polyester foil over stranded bundle
-
Cu braid, bare
PVC
app. 8,0 mm ± 0,3 mm
Pastel turquoise similar to RAL 6034

100 Ohm ± 15 Ohm
96 Ohm/km
1 GOhm x km
192 Ohm/km max.
60 nF/km nom.
1 kV
256 kHz < 15,0 dB/km
772 kHz < 24,0 dB/km
1 MHz < 27,0 dB/km
4 MHz < 52,0 dB/km
10 MHz < 84,0 dB/km
16 MHz < 112,0 dB/km
20 MHz < 119,0 dB/km

app. 96 kg/km
120 mm
-40°C
+70°C
1,31 MJ/m
68,00 kg/km

interbus specification 2.0, IEC61158
Flame-retardant acc. to IEC 60332-1-2
UL Style 2571
-

81202, I-BUS