



Type

RJ-45 UP socket cat. 5e 2P horizontal

RJ-45 UP socket cat. 5e 2P vertical

Configuration

Housing material:
Colour:
Board:
Push-on connector type:
Outlet direction:
Number of bushes:
Type of screen:
Strain relief:
Cable inlet:

Die-cast, shielded
Pure White similar to RAL 9010
1x2
RJ45(8/8)
45 degrees
2
Overall screen
via pre-installed cable clips
horizontal

Die-cast, shielded
Pure White similar to RAL 9010
1x2
RJ45(8/8)
45 degrees
2
Overall screen
via pre-installed cable clips
vertical

Connecting system

Connection type:
Suitable for cable diameter:
Insulation diameter, min.:

LSA plus - insulation piercing connections
0,4 - 0,64mm (AWG 26 - 22)
0,7 - 1,1 mm (PE)

LSA plus - insulation piercing connections
0,4 - 0,64mm (AWG 26 - 22)
0,7 - 1,1 mm (PE)

Assignment type

EIA/TIA 568 A + EIA/TIA 568 B

EIA/TIA 568 A + EIA/TIA 568 B

Dimension

Dimensions of central plate:
Installation dimensions:

50 x 50mm
51 x 51 x 29mm

50 x 50mm
51 x 51 x 29mm

Norms and standards

HELUKAT® CONNECTING SYSTEMS® system component up to 100 MHz in category 5(e) / Class D in accordance with ISO 11801, 2nd edition, EN 50173, 2nd edition, EIA/TIA 568 B, and EN 55022 (EMC)

Application

As workstation interface in applications of digital and analog image, data and voice transmission. Available as in-wall version (channel) and top-mount version (wall).

Part no.

82008

82853

Dimensions and specifications may be changed without prior notice.

Packing unit

10

10