

SPRO - 3:1



TECHNICAL DATA

Polyolefin shrink tube 3:1

Temperature range -55°C to +135°C

■ STRUCTURE

- Material: Polyolefin

■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction
- for repairing insulation
- for sealing electrical components

Inner Ø before shrinkage mm	Wall thickness mm	Inner Ø after shrinkage mm	Packaging unit (in m)	green-yellow	black	blue	yellow	red	green
				Part no.	Part no.	Part no.	Part no.	Part no.	Part no.
6.4	0.65	2.0	75.0	903093	903035	903031	903032	903033	903039
9.5	0.75	3.0	75.0	903094	903045	903041	903042	903043	903049
12.7	0.75	4.0	50.0	903095	903055	903051	903052	903053	903059
19.0	0.85	6.0	30.0	903096	903065	903061	903062	903063	903069
25.4	1.0	8.0	30.0	903097	903075	903071	903072	903073	903079
39.0	1.15	13.0	30.0	903098	903085	903081	903082	903083	903089