


# LAN Cable

Category 8

**HELUKAT® 1200** 

S/FTP




## Cable structure

Inner conductor Ø:	0,64 mm
Conductor material:	Copper, bare
Core insulation:	Foam-skin-PE
Core colours:	wh/bu, wh/og, wh/gn, wh/bn
Separator:	-
Screen over stranding element:	Al-Foil
Screen 1 over stranding:	Cu braid
Screen 2 over stranding:	-
Outer sheath material:	FRNC
Outer diameter:	app. 7,7 mm
Outer sheath colour:	Blue similar to RAL 5015

## S/FTP 4x2xAWG 22/1 FRNC

## Electrical data

Characteristic impedance:	100 Ohm ± 15 Ohm at 1 to 100 MHz 100 Ohm ± 20 Ohm at 101 to 1200 MHz
Loop resistance:	120 Ohm/km max.
Mutual capacitance:	43 nF/km nom.
Rel. propagation velocity:	79 %



## Typical values


Frequency (MHz)	10	16	62,5	100	200	300	600	1000	1200
Attenuation (db/100m)	4,9	6,3	12,7	16,3	23,5	29,4	42,8	53,0	59,0
Next (db)	100,0	100,0	95,0	93,0	90,0	87,0	81,0	78,0	77,0
ACR (db)	95,1	93,7	82,3	76,7	66,5	57,6	38,2	25,0	18,0

## Technical data

Weight:	app. 66 kg/km
bending radius, repeated:	72 mm
Operating temperature range min.:	-20°C
Operating temperature range max.:	+60°C
Caloric load, approx. value:	0,70 MJ/m
Copper weight:	40,00 kg/km

## Norms

Acc. to ISO/IEC 11801, Acc. to EN 50173, Acc. to EIA/TIA 568-A, Category 7e, Flame-retardant acc. to IEC 60332-3, Smoke density acc. to IEC 61034, Halogen-free acc. to 60754-2, Corrosiveness acc. to EN50267-2-3



## Application

HELUKAT® 1200 data cables are used in the tertiary, but also in the secondary level of a network. They are characterized by large performance reserves and outstanding performance. They can be used to implement services such as Gigabit Ethernet, Fast Ethernet, Ethernet, ATM155, FDDI, token ring 4/16 Mbit/s or ISDN absolutely trouble-free. Likewise, the mechanical characteristics are perfectly suited for the application in tight cable channels and platforms due to their optimized construction.

## Part no.

**81699**, S/FTP 4x2xAWG 22/1 FRNC (S-FTP)

Dimensions and specifications may be changed without prior notice.