



BUS Cables

Profibus drag chain ET200X + ECOFAST

 **HELUKABEL®**

PUR



Type Cable structure

Inner conductor diameter 1:
Inner conductor diameter 2:
Core insulation 1:
Core insulation 2:
Core colours 1:
Core colours 2:
Stranding element 1:
Separator:
Shielding 1:
Total shielding:
Outer sheath material:
Cable external diameter:
Outer sheath colour:

Electrical data

Characteristic impedance:
Conductor resistance, max.:
Insulation resistance, min.:
Loop resistance:
Mutual capacitance:
Test voltage:
Relative propagation velocity:
Attenuation:

Technical data

Weight:
bending radius, repeated:
Operating temperature range min.:
Operating temperature range max.:
Caloric load, approx. value:
Copper weight:

Norms

Applicable standards:

UL Style:

Application

HELUKABEL® Profibus ET200X + Ecofast Hybrid cables are designed for continuous motion in cable carriers. The hybrid construction integrates the power supply next to the Profibus in one cable. The type ET200X offers three 0,75mm² power conductors, while the type Ecofast 4 has 1,5mm² power conductors and greater current-carrying capacity.

Part no.

Dimensions and specifications may be changed without prior notice.

Drag chain applications 1x2x0.65 mm + 3x1x0.75 mm² (stranded)

Copper, bare (AWG 24/19)
Copper, bare (AWG 18/42)
Foam-skin-PE
PE
rd, gn
bk, bu, gnye
Double core
Polyester foil over stranded bundle
AL-Foil + braid
Polyester foil
PUR
app. 9,7 mm ± 0,3 mm
Petrol similar to RAL 5018

150 Ohm ± 10 %
73 Ohm/km
5 GOhm x km
145 Ohm/km max.
30 nF/km nom.
1,5 kV
-
9,6 kHz < 3,0 dB/km
38,4 kHz < 5,0 dB/km
4 MHz < 25,0 dB/km
16 MHz < 52,0 dB/km

app. 106 kg/km
145 mm
-15°C
+60°C
1,953 MJ/m
46,00 kg/km

Profibus acc. to DIN 19245 T3 and EN50170
Halogen-free acc. to 60754-1
Flame-retardant acc. to IEC 60332-1-2
AWM 21814 80°C 30V I/II A/B FT2

Drag chain applications 1x2x0.65 mm + 4x1x1.5 mm² (stranded)

Copper, bare (AWG 24/19)
Copper, bare (AWG 18/85)
Foam-skin-PE
PE
rd, gn
bk, bk, bk, bk
2 cores + 2 fillers stranded together
Polyester foil over stranded bundle
AL-Foil + braid
-
PUR
app. 11,5 mm ± 0,3 mm
Violet similar to RAL 4001

150 Ohm ± 15 %
73 Ohm/km
1 GOhm x km
145 Ohm/km max.
30 nF/km nom.
1,5 kV
81 %
9,6 kHz < 3,0 dB/km
38,4 kHz < 5,0 dB/km
4 MHz < 25,0 dB/km
16 MHz < 49,0 dB/km

app. 160 kg/km
173 mm
-30°C
+70°C
2,835 MJ/m
90,00 kg/km

Profibus acc. to DIN 19245 T3 and EN50170
Halogen-free acc. to 60754-1
Flame-retardant acc. to IEC 60332-1-2
UL Style 20233

800044, Profibus L2