

RE hexagonal

Transition from large to small thread



TECHNICAL DATA

Nickel plated hexagonal brass reducer

Temperature range up to +200°C

■ STRUCTURE

- Material: Brass, nickel plated

■ APPLICATION

- Machine and plant construction
- Automation technology
- Vehicle construction and shipbuilding
- Installation technology

■ NOTES

- Legend:
Dimensions
TD - Thread Diameter
SI - Size of the internal thread

from metric to metric

Part no.	Size outside	Size inside	Thread length mm	Spanner size mm	Packaging unit (in pc.)
904380	M16 x 1.5	M12 x 1.5	6.5	17	100
904381	M20 x 1.5	M12 x 1.5	7.0	22	100
904382	M20 x 1.5	M16 x 1.5	6.0	22	100
904383	M25 x 1.5	M16 x 1.5	7.0	27	50
904384	M25 x 1.5	M20 x 1.5	7.0	27	50
94073	M32 x 1.5	M20 x 1.5	8.0	35	50
94946	M32 x 1.5	M25 x 1.5	8.0	35	50

Part no.	Size outside	Size inside	Thread length mm	Spanner size mm	Packaging unit (in pc.)
94076	M40 x 1.5	M25 x 1.5	8.0	43	25
90909	M40 x 1.5	M32 x 1.5	8.0	43	25
904385	M50 x 1.5	M32 x 1.5	10.0	54	10
90865	M50 x 1.5	M40 x 1.5	10.0	54	25
94947	M63 x 1.5	M40 x 1.5	10.0	65	10
904386	M63 x 1.5	M50 x 1.5	10.0	65	10

from PG to PG

Part no.	Size outside	Size inside	Thread length mm	Spanner size mm	Packaging unit (in pc.)
904387	PG 9	PG 7	6.0	17	100
904388	PG 11	PG 7	6.0	20	100
904389	PG 11	PG 9	6.0	20	100
904392	PG 13.5	PG 11	6.5	22	100
904390	PG 13.5	PG 7	6.0	22	50
904391	PG 13.5	PG 9	6.5	22	100
904395	PG 16	PG 11	6.5	24	100
904396	PG 16	PG 13.5	6.5	24	100
904393	PG 16	PG 7	6.5	24	50
904394	PG 16	PG 9	6.5	24	100
904397	PG 21	PG 11	7.0	30	100

Part no.	Size outside	Size inside	Thread length mm	Spanner size mm	Packaging unit (in pc.)
904398	PG 21	PG 13.5	7.0	30	100
904399	PG 21	PG 16	7.0	30	100
92888	PG 29	PG 16	8.0	40	50
904400	PG 29	PG 21	8.0	40	50
904401	PG 36	PG 21	9.0	50	25
904402	PG 36	PG 29	9.0	50	25
904403	PG 42	PG 29	10.0	57	25
904404	PG 42	PG 36	10.0	57	25
904405	PG 48	PG 36	10.0	64	25
904406	PG 48	PG 42	10.0	64	10