


KM-EMV



TECHNICAL DATA

Nickel plated brass EMC counternut

Temperature range up to +200°C

■ STRUCTURE

- Material: Brass, nickel plated
- with cutting edges

■ PROPERTIES

- increased vibration resistance

■ APPLICATION

- For secure fixing of EMC cable glands. For cutting through painted surfaces to ensure optimum contact with equipotential bonding.

■ NOTES

- Legend:
Dimensions
TD - Thread Diameter
SZ - Spanner Size

metric thread – female

Size	Spanner size mm	Packaging unit (in pc.)	Part no.
M12 x 1.5	15	100	90165
M16 x 1.5	19	100	90166
M20 x 1.5	24	100	90167
M25 x 1.5	30	100	90168

Size	Spanner size mm	Packaging unit (in pc.)	Part no.
M32 x 1.5	36	100	90169
M40 x 1.5	46	25	90170
M50 x 1.5	60	10	90171
M63 x 1.5	70	10	90172

metric thread – female – for large cable diameters

Size	Spanner size mm	Packaging unit (in pc.)	Part no.
M72 x 2.0	80	10	99875
M75 x 1.5	80	10	93209

Size	Spanner size mm	Packaging unit (in pc.)	Part no.
M80 x 2.0	95	1	98698

PG thread – female

Size	Spanner size mm	Packaging unit (in pc.)	Part no.
PG 7	15	100	97243
PG 9	18	100	97244
PG 11	21	100	97166
PG 13.5	23	100	97167
PG 16	26	100	97168

Size	Spanner size mm	Packaging unit (in pc.)	Part no.
PG 21	32	100	97169
PG 29	41	100	97170
PG 36	51	25	97171
PG 42	60	10	97245
PG 48	64	10	97246