



## TECHNICAL DATA

### Stainless steel cable gland

<b>Temperature range</b>	-20°C to +100°C short term -40°C to +150°C
<b>Protection class</b>	IP 68 - 5 bar, 30 min. / IP 69K

## ■ STRUCTURE

- Material: Stainless steel 1.4305 / AISI 303
- Seal: thermoplastic elastomers (TPE)

## ■ PROPERTIES

- optimal strain relief through strain relief element
- easy to assemble, time and cost savings
- watertight, dust-tight
- protection against ingress of water and foreign material into enclosure
- smooth surface prevents to adhere harmful microorganisms and allows for easy cleaning
- internal thread prevents dirt accumulation
- suitable for high pressure steam cleaning
- resistant against chemical cleaning supplies
- high corrosion resistance
- ECOLAB certified

## ■ APPLICATION

- Food and beverage industry
- Pharmaindustrie
- Reinraumtechnologie
- Biotechnologie
- chemical industry
- Highest requirements to cleanliness and cleaning.

## ■ NOTES

- for tightening from outside use the listed tightening tool
- assembly with commercial socket wrench
- delivery including counter nut
- Legend:  
Dimensions  
D - Outer diameter of upper part  
D2 - Inner diameter of thread  
D4 - Inner diameter of upper part  
H - Height without thread  
TL - Thread Length  
SZ - Spanner Size

### metric thread

Part no.	Size	Cable Ø from / to mm	Thread length mm	Spanner size mm	Outer Ø of upper part mm	Inner Ø of upper part mm	Inner Ø of thread mm	Hight without thread mm	Recom- mended cap counter nut Nm	Packaging unit (in pc.)
906918	M16 x 1.5	5.0 - 10.0	7.0	18	20.2	10.3	10	34.5	4	5
906919	M20 x 1.5	6.0 - 12.0	8.0	22	24.1	12.3	13	35.5	5	5
906920	M25 x 1.5	12.0 - 17.0	10.0	28	30.1	17.3	17	41	6	5