



## TECHNICAL DATA

### Nickel plated brass sealing gland

Temperature range	-40°C to +135°C
Protection class	IP 68 - 10 bar

## ■ STRUCTURE

- Material: Brass, nickel plated
- Seal: thermoplastic vulcanizates (TPV)
- with inserts made of TPV, profile fits to ASI- bus line

## ■ PROPERTIES

- optimum strain relief through rubber seal
- easy to assemble, time and cost savings
- Large-area sealing

## ■ TESTS

- Test standard EN 62444

## ■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Installation technology
- Control cabinet construction

## ■ NOTES

- Legend:  
Dimensions  
TD - Thread Diameter  
TL - Thread Length  
SZ - Spanner Size

### metric thread

Part no.	Size	Sealing insert colour	Cable Ø from / to mm	Thread length mm	Spanner size mm	Packaging unit (in pc.)
904121	M20 x 1.5	grey, left	-	6.5	22	50
904122	M20 x 1.5	grey, right	-	6.5	22	50

### PG thread

Part no.	Size	Sealing insert colour	Cable Ø from / to mm	Thread length mm	Spanner size mm	Packaging unit (in pc.)
904123	PG 13.5	grey, left	-	6.5	22	50
904124	PG 13.5	grey, right	-	6.5	22	50