

# LT-FG-Clean



## TECHNICAL DATA

### Stainless steel- conduit gland

Temperature range	-45°C to +105°C
Protection class	IP 68 - 40 bar

## ■ STRUCTURE

- Material: Stainless steel
- Grounding sleeve: steel

## ■ PROPERTIES

- high corrosion resistance
- resistant to: chemical cleaning supplies

## ■ APPLICATION

- Food and beverage industry
- Pharmaindustrie
- chemical industry
- Highest requirements to cleanliness and cleaning.

## ■ NOTES

- Ferrule: brass, nickel plated
- Clamping ring and insert: PA 6
- Outer seal and sealing ring: TPE according to FDA 21 CFR and NSF 51 (USA-Norm)
- The smooth surface prevents to adhere harmful micro organisms
- Easy, fast and less expensive cleaning supplies
- No threads are exposed
- High tightness
- No enter from water and dirt from outside
- High mechanical load capacity
- Suitable protection tubes:  
Anaconda Sealtite FG-Clean, also possible EF, HTDL, OR, HC, HXC, ZHLS, HFX

### metric thread

Part no.	Size	Suitable for tube ND	Suitable for tube outer Ø mm	Inner Ø mm	Spanner size mm	Thread length mm	Height mm	Angle size mm	Packaging unit (in pc.)
906928	M16 x 1.50	3/8	17.8	10.4	27	12.0	48	31.0	10
906929	M20 x 1.50	1/2	21.1	13.8	30	13.0	50	34.0	10
906843	M25 x 1.50	3/4	26.4	18.5	36	15.0	57	41.0	5
906844	M32 x 1.50	1	33.1	23.8	46	15.0	68	53.0	5
906845	M40 x 1.50	1 1/4	41.8	31.8	54	16.0	75	62.0	2
906846	M50 x 1.50	1 1/2	47.8	36.8	63	18.0	81	70.0	2