



TECHNICAL DATA

Nickel plated brass sealing gland

Temperature range -40°C to +130°C
Protection class IP 65

■ STRUCTURE

- Material: Brass, nickel plated
- Seal: thermoplastic elastomers (TPE)
- with multiple TPE sealing inserts

■ PROPERTIES

- optimum strain relief through rubber seal
- easy to assemble, time and cost savings
- Large-area sealing

■ TESTS

- Test standard EN 62444

■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction

■ NOTES

- Protection classification IP 68, provided that the bore diameter in the sealing insert area is equal to the cable diameter.
- Legend:
Dimensions
TD - Thread Diameter
TL - Thread Length
SZ - Spanner Size

metric thread

Part no.	Size	Number holes x cable-Ø mm	Thread length mm	Spanner size mm	Packaging unit (in pc.)
904125	M16 x 1.5	2 x 1.2	9.0	19	50
904126	M16 x 1.5	2 x 3.0	9.0	19	50
905024	M16 x 1.5	3 x 3.0	9.0	19	50
904127	M16 x 1.5	4 x 3.0	6.0	19	50
904128	M16 x 1.5	2 x 4.0	9.0	19	50
904129	M16 x 1.5	1 x 5.0	9.0	19	50
904130	M20 x 1.5	6 x 2.0	9.0	24	50
904131	M20 x 1.5	2 x 2.3	9.0	24	50
904132	M20 x 1.5	6 x 2.5	9.0	24	50
904133	M20 x 1.5	2 x 3.0	9.0	24	50
904134	M20 x 1.5	3 x 3.0	9.0	24	50
904135	M20 x 1.5	2 x 5.0	9.0	24	50
904136	M25 x 1.5	7 x 2.0	9.0	30	50
904137	M25 x 1.5	2 x 4.0	9.0	30	50
904138	M25 x 1.5	4 x 4.0	9.0	30	50
904139	M25 x 1.5	6 x 4.0	9.0	30	50
904140	M25 x 1.5	2 x 6.0	9.0	30	50
904141	M25 x 1.5	3 x 7.0	9.0	30	50
904142	M32 x 1.5	21 x 2.0	11.0	36	25
904143	M32 x 1.5	8 x 3.0	11.0	36	25

UNI-DICHT-MFD-MS



Part no.	Size	Number holes x cable-Ø mm	Thread length mm	Spanner size mm	Packaging unit (in pc.)
904144	M32 x 1.5	6 x 4.0	11.0	36	25
904145	M32 x 1.5	8 x 4.0	11.0	36	25
904146	M32 x 1.5	4 x 5.0	11.0	36	25
904147	M32 x 1.5	4 x 6.0	11.0	36	25
904148	M32 x 1.5	6 x 6.5	11.0	36	25
904149	M32 x 1.5	3 x 7.0	11.0	36	25
904150	M32 x 1.5	4 x 8.0	11.0	36	25
904151	M32 x 1.5	2 x 9.0	11.0	36	25
904152	M40 x 1.5	6 x 6.0	11.5	46	10
904153	M40 x 1.5	10 x 6.0	11.5	46	10
904154	M40 x 1.5	4 x 6.5	11.5	46	10
904155	M40 x 1.5	6 x 8.0	11.5	46	10
904156	M40 x 1.5	4 x 9.0	11.5	46	10
904157	M40 x 1.5	5 x 9.0	11.5	46	10
904158	M40 x 1.5	5 x 10.0	11.5	46	10
904159	M40 x 1.5	2 x 11.0	11.5	46	10
904160	M50 x 1.5	15 x 5.0	14.0	55	5
904161	M50 x 1.5	8 x 9.0	14.0	55	5
904162	M50 x 1.5	3 x 10.0	14.0	55	5
904163	M50 x 1.5	2 x 15.0	14.0	55	5

PG thread

Part no.	Size	Number holes x cable-Ø mm	Thread length mm	Spanner size mm	Packaging unit (in pc.)
904164	PG 9	2 x 1.2	9.0	19	50
904165	PG 9	2 x 3.0	9.0	19	50
904166	PG 9	4 x 3.0	9.0	19	50
904167	PG 9	2 x 4.0	9.0	19	50
904168	PG 9	1 x 5.0	9.0	19	50
904169	PG 11	6 x 2.0	9.0	22	50
904170	PG 11	2 x 2.3	9.0	22	50
904171	PG 11	6 x 2.5	9.0	22	50
904172	PG 11	2 x 3.0	9.0	22	50
904173	PG 11	3 x 3.0	9.0	22	50
904174	PG 11	2 x 5.0	9.0	22	50
904175	PG 13.5	3 x 2.0	9.0	24	50
904176	PG 13.5	10 x 2.0	9.0	24	50
904177	PG 13.5	2 x 3.0	9.0	24	50
904178	PG 13.5	3 x 3.0	9.0	24	50
904179	PG 13.5	6 x 3.5	9.0	24	50
904180	PG 13.5	2 x 5.0	9.0	24	50
904181	PG 13.5	2 x 6.0	9.0	24	50
904182	PG 16	7 x 2.0	9.0	27	50
904183	PG 16	2 x 4.0	9.0	27	50
904184	PG 16	4 x 4.0	9.0	27	50
904185	PG 16	6 x 4.0	9.0	27	50
904186	PG 16	2 x 6.0	9.0	27	50
904187	PG 16	3 x 7.0	9.0	27	50
904188	PG 21	21 x 2.0	11.0	33	25
904189	PG 21	8 x 3.0	11.0	33	25
904190	PG 21	6 x 4.0	11.0	33	25
904191	PG 21	8 x 4.0	11.0	33	25
904192	PG 21	4 x 5.0	11.0	33	25
904193	PG 21	4 x 6.0	11.0	33	25
904194	PG 21	6 x 6.5	11.0	33	25
904195	PG 21	3 x 7.0	11.0	33	25
904196	PG 21	4 x 8.0	11.0	33	25
904197	PG 21	2 x 9.0	11.0	33	25
904198	PG 29	6 x 6.0	11.0	43	10
904199	PG 29	10 x 6.0	11.0	43	10
904200	PG 29	4 x 6.5	11.0	43	10
904201	PG 29	6 x 8.0	11.0	43	10
904202	PG 29	4 x 9.0	11.0	43	10
904203	PG 29	5 x 9.0	11.0	43	10
904204	PG 29	5 x 10.0	11.0	43	10
904205	PG 29	2 x 11.0	11.0	43	10

Continued on next page

UNI-DICHT-MFD-MS



Part no.	Size	Number holes x cable-Ø mm	Thread length mm	Spanner size mm	Packaging unit (in pc.)
904207	PG 36	15 x 5.0	14.0	53	10
904206	PG 36	8 x 9.0	14.0	53	10
904208	PG 36	3 x 10.0	14.0	53	10
904209	PG 36	2 x 15.0	14.0	53	10