



TECHNICAL DATA

PA cable gland acc. to DIN 46320

Temperature range -20°C to +80°C
 Protection class IP 54

■ STRUCTURE

- Material: Polyamide (PA)
- Seal: Natural rubber (NR)
- with incision sealing ring

■ PROPERTIES

- halogen-free
- phosphor-free
- silicone-free
- cadmium-free
- large clamping areas

■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction

■ NOTES

- Protection classification IP 65 with an additional O-ring on the external thread.
- Legend:
 Dimensions
 TD - Thread Diameter
 TL - Thread Length
 SZ - Spanner Size

PG thread

Size	Cable Ø from / to mm	Thread length mm	Spanner size mm	Packaging unit (in pc.)	grey (RAL 7035) Part no.
PG 9	4.0 - 10.0	8.0	19 / 16	50	904231
PG 11	6.5 - 12.0	8.0	22 / 19	50	904232
PG 13.5	6.5 - 13.5	9.0	24 / 21	50	904233
PG 16	6.5 - 16.0	10.0	27 / 23	50	904234
PG 21	9.0 - 20.0	11.0	33 / 30	50	904235
PG 29	17.0 - 28.0	11.0	42 / 40	25	904236
PG 36	23.0 - 34.0	13.0	53 / 50	10	904237
PG 42	29.0 - 40.0	13.0	60 / 55	5	904238
PG 48	35.0 - 46.0	14.0	65 / 60	5	904239