

# Adapter round

for thread adjustment from metric to PG



## TECHNICAL DATA

Nickel plated round brass adapter

Temperature range up to +200°C

### ■ STRUCTURE

- Material: Brass, nickel plated

### ■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction

### ■ NOTES

- Legend:  
Dimensions  
TD - Thread Diameter  
SI - Size of the internal thread

#### from metric to PG

Part no.	Size outside	Size inside	Thread length mm	Outer Ø mm, approx.	Packaging unit (in pc.)
904343	M16 x 1.5	PG 7	6.5	18.0	100
904344	M20 x 1.5	PG 7	7.0	22.0	100
904345	M20 x 1.5	PG 9	7.0	22.0	100
904347	M25 x 1.5	PG 11	7.5	27.0	50
904348	M25 x 1.5	PG 13.5	7.5	27.0	50
904349	M25 x 1.5	PG 16	7.5	27.0	50
904346	M25 x 1.5	PG 9	7.5	27.0	50
904350	M32 x 1.5	PG 13.5	8.0	34.0	50

Part no.	Size outside	Size inside	Thread length mm	Outer Ø mm, approx.	Packaging unit (in pc.)
904351	M32 x 1.5	PG 16	8.0	34.0	50
904352	M32 x 1.5	PG 21	8.0	34.0	50
904353	M40 x 1.5	PG 16	8.0	43.0	25
904354	M40 x 1.5	PG 21	8.0	43.0	25
904355	M50 x 1.5	PG 21	9.0	53.0	10
904356	M50 x 1.5	PG 29	9.0	53.0	10
904357	M63 x 1.5	PG 29	10.0	66.0	10
904359	M63 x 1.5	PG 42	10.0	66.0	10

#### from metric to PG - high-profile design

Part no.	Size outside	Size inside	Thread length mm	Outer Ø mm, approx.	Packaging unit (in pc.)
904360	M12 x 1.5	PG 7	5.0	14.0	100
904361	M12 x 1.5	PG 9	6.0	18.0	100
904363	M16 x 1.5	PG 11	5.0	20.0	100
904362	M16 x 1.5	PG 9	5.0	18.0	100
904365	M20 x 1.5	PG 13.5	6.0	22.0	100
904366	M20 x 1.5	PG 16	6.0	24.0	100
904367	M25 x 1.5	PG 21	7.0	30.0	50

Part no.	Size outside	Size inside	Thread length mm	Outer Ø mm, approx.	Packaging unit (in pc.)
904368	M32 x 1.5	PG 29	8.0	39.0	50
904369	M40 x 1.5	PG 29	8.0	43.0	25
904370	M40 x 1.5	PG 36	8.0	50.0	25
904371	M50 x 1.5	PG 36	9.0	53.0	10
904372	M50 x 1.5	PG 42	9.0	57.0	10
904373	M63 x 1.5	PG 48	10.0	68.0	10

# Adapter round

## for thread adjustment from metric to PG

### from PG to metric

Part no.	Size outside	Size inside	Thread length mm	Outer Ø mm, approx.	Packaging unit (in pc.)
904374	PG 11	M20 x 1.5	6.0	22.0	100
904375	PG 13.5	M20 x 1.5	6.5	24.0	50

Part no.	Size outside	Size inside	Thread length mm	Outer Ø mm, approx.	Packaging unit (in pc.)
94098	PG 16	M20 x 1.5	6.5	24.0	50
94102	PG 21	M25 x 1.5	7.0	30.0	100

### from PG to metric - high-profile design

Part no.	Size outside	Size inside	Thread length mm	Outer Ø mm, approx.	Packaging unit (in pc.)
904377	PG 11	M20 x 1.5	6.5	22.0	100
904378	PG 13.5	M20 x 1.5	6.5	22.0	100

Part no.	Size outside	Size inside	Thread length mm	Outer Ø mm, approx.	Packaging unit (in pc.)
904379	PG 16	M25 x 1.5	6.5	27.0	50
904376	PG 9	M16 x 1.5	6.0	20.0	100