



TECHNICAL DATA

Tubular cable lug

Flange shape Ring shape
 Connecting angle 180° (horizontal)
 Temperature range up to +120°C

STRUCTURE

- Material: copper acc. to DIN EN 13600
- Surface: galvanic tin plated
- uninsulated
- without Inspection hole

TESTS

- certifications and approvals:
 UL File Number E504132

NOTES

- Recommended pressing method: WM pressing
- Legend:
 a - Diameter of stud hole
 b - Width of flange
 d - Inner diameter of wire receptacle
 l - Length to centre of hole

Part no.	Cross-sec. mm ²	Stud hole (M)	Ø Stud hole (a) in mm	Flange width (b) in mm	Ø Wire receptacle (d) in mm	Length (l) in mm	Weight in kg/1000 pc.	Packaging unit (in pc.)
907318	6	4	4.3	10.0	3.5	19.0	4.6	100
907319	6	5	5.3	10.0	3.5	20.0	4.7	100
907320	6	6	6.4	11.0	3.5	21.5	5.4	100
907321	6	8	8.4	15.0	3.5	24.0	5.9	100
907322	6	10	10.5	18.0	3.5	26.0	6.4	100
907323	6	12	13.0	19.0	3.5	27.5	6.4	100
907324	10	4	4.3	12.0	4.5	20.0	4.3	100
907325	10	5	5.3	12.0	4.5	21.0	4.8	100
907326	10	6	6.4	12.0	4.5	22.5	5.1	100
907327	10	8	8.4	15.0	4.5	25.0	5.8	100
907328	10	10	10.5	18.0	4.4	27.0	6.3	100
907329	10	12	13.0	20.0	4.5	28.5	6.3	100
907330	16	4	4.3	12.0	5.5	24.0	8.2	100
907331	16	5	5.3	12.0	5.5	25.0	8.9	100
907332	16	6	6.4	12.0	5.5	26.5	9.6	100
907333	16	8	8.4	15.0	5.5	29.0	10.3	100
907334	16	10	10.5	18.0	5.5	31.0	11.0	100
907335	16	12	13.0	19.0	5.5	32.0	10.8	100
907336	25	5	5.3	15.0	7.0	33.5	13.5	100
907337	25	6	6.4	15.0	7.0	31.5	13.1	100
907338	25	8	8.4	16.0	7.0	33.0	12.9	100
907339	25	10	10.5	18.0	7.0	34.5	14.6	100
907340	25	12	13.0	20.0	7.0	36.0	15.5	100
907341	25	14	15.0	22.0	7.0	39.0	16.6	100
907342	25	16	17.0	24.0	7.0	42.0	17.3	100
907343	35	6	6.4	17.0	8.5	33.0	20.7	100
907344	35	8	8.4	17.0	8.5	34.0	21.8	100

HELU-S-RK-CU-UL



Part no.	Cross-sec. mm ²	Stud hole (M)	∅ Stud hole (a) in mm	Flange width (b) in mm	∅ Wire receptable (d) in mm	Length (l) in mm	Weight in kg/1000 pc.	Packaging unit (in pc.)
907345	35	10	10.5	20.0	8.5	36.5	21.9	100
907346	35	12	13.0	22.0	8.5	37.5	23.3	100
907347	35	14	15.0	23.0	8.5	40.0	24.4	100
907348	35	16	17.0	28.0	8.5	44.0	26.0	100
907349	50	6	6.4	20.0	10.0	37.0	30.1	100
907350	50	8	8.4	20.0	10.0	39.0	30.4	100
907351	50	10	10.5	20.0	10.0	40.5	31.3	100
907352	50	12	13.0	23.0	10.0	42.0	31.3	100
907353	50	14	15.0	23.0	10.0	44.0	35.1	100
907354	50	16	17.0	27.0	10.0	46.0	35.5	100
907355	50	20	21.0	30.5	10.0	52.5	38.9	100
907356	70	6	6.4	24.0	12.0	40.5	41.1	25
907357	70	8	8.4	24.0	12.0	42.5	44.6	25
907358	70	10	10.5	24.0	12.0	43.5	46.4	25
907359	70	12	13.0	24.0	12.0	45.0	47.3	25
907360	70	14	15.0	25.0	12.0	46.0	49.1	25
907361	70	16	17.0	28.0	12.0	48.5	49.6	25
907362	70	20	21.0	29.0	12.0	52.0	52.9	25
907363	95	6	6.4	26.0	13.5	43.0	49.5	25
907364	95	8	8.4	26.0	13.5	46.0	53.6	25
907365	95	10	10.5	26.0	13.5	47.0	55.1	25
907366	95	12	13.0	26.0	13.5	48.0	55.1	25
907367	95	14	15.0	26.0	13.5	51.5	58.9	25
907368	95	16	17.0	28.0	13.5	51.0	58.5	25
907369	95	20	21.0	30.0	13.5	55.0	61.3	25
907370	120	8	8.4	29.0	15.0	49.5	68.8	25
907371	120	10	10.5	29.0	15.0	52.0	79.9	25
907372	120	12	13.0	29.0	15.0	51.5	78.4	25
907373	120	14	15.0	30.0	15.0	53.0	78.6	25
907374	120	16	17.0	30.0	15.0	55.0	80.7	25
907375	120	20	21.0	35.0	15.0	60.0	89.0	25
907376	150	8	8.4	31.0	16.8	55.5	78.9	25
907377	150	10	10.5	31.0	16.8	56.5	83.7	25
907378	150	12	13.0	31.0	16.8	56.0	80.7	25
907379	150	14	15.0	31.0	16.8	57.0	83.0	25
907380	150	16	17.0	31.0	16.8	58.0	83.6	25
907381	150	20	21.0	35.0	16.8	63.0	87.5	25
907382	185	8	8.4	35.0	19.0	58.0	103.7	25
907383	185	10	10.5	35.0	19.0	59.0	106.1	25
907384	185	12	13.0	35.0	19.0	58.5	106.0	25
907385	185	14	15.0	35.0	19.0	61.0	107.2	25
907386	185	16	17.0	35.0	19.0	63.0	108.6	25
907387	185	20	21.0	35.0	19.0	66.0	113.3	25
907388	240	8	8.4	38.0	21.0	67.0	124.0	25
907389	240	10	10.5	38.0	21.0	67.0	129.7	25
907390	240	12	13.0	38.0	21.0	67.0	130.2	25
907391	240	14	15.0	38.0	21.0	69.0	133.6	25
907392	240	16	17.0	38.0	21.0	69.5	135.6	25
907393	240	20	21.0	38.0	21.0	71.0	138.0	25
907394	300	10	10.5	44.0	24.0	79.5	204.5	20
907395	300	12	13.0	44.0	24.0	82.0	211.8	20
907396	300	14	15.0	44.0	24.0	84.0	221.9	20
907397	300	16	17.0	44.0	24.0	85.0	219.4	20
907398	300	20	21.0	44.0	24.0	85.0	224.0	20
907399	400	10	10.5	49.0	27.5	92.0	279.0	15
907400	400	12	13.0	49.0	27.5	92.0	278.5	15
907401	400	16	17.0	49.0	27.5	92.0	276.5	15
907402	400	20	21.0	49.0	27.5	92.0	266.1	15
907404	500	16	17.0	55.5	31.0	113.0	493.8	5
907405	500	20	21.0	55.5	31.0	113.0	485.6	5

22.08.2022 / We reserve the right to make technical changes; the imprint in the image is purely exemplary