


Adapter PA-ATEX

for thread adjustment from PG to metric



TECHNICAL DATA

PA EX adapter

Temperature range -20°C to +70°C
Protection class IP 66

STRUCTURE

- Material: Polyamide (PA)

PROPERTIES

- halogen-free
- phosphor-free
- silicone-free
- cadmium-free

APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Installation technology
- Control cabinet construction

NOTES

- Approval: PTB 04 ATEX 1040 X
- Legend:
Dimensions
TD - Thread Diameter
SI - Size of the internal thread

from PG to metric

Size outside	Size inside	Packaging unit (in pc.)	black (RAL 9005) Part no.
PG 21	M20 x 1.5	10	904449
PG 29	M20 x 1.5	10	904450
PG 29	M25 x 1.5	10	904451
PG 29	M32 x 1.5	10	904452
PG 36	M25 x 1.5	10	904454
PG 36	M32 x 1.5	10	904455
PG 36	M40 x 1.5	10	904456
PG 42	M20 x 1.5	5	904457
PG 42	M25 x 1.5	5	904458
PG 42	M32 x 1.5	5	904459
PG 42	M40 x 1.5	5	904460
PG 48	M20 x 1.5	5	904461
PG 48	M25 x 1.5	5	904462
PG 48	M32 x 1.5	5	904463
PG 48	M40 x 1.5	5	904464

Adapter PA-ATEX

for thread adjustment from PG to metric



from PG to metric - high-profile design

Size outside	Size inside	Packaging unit (in pc.)	black (RAL 9005) Part no.
PG 9	M12 x 1.5	25	904468
PG 9	M16 x 1.5	25	904469
PG 9	M20 x 1.5	25	904470
PG 11	M16 x 1.5	25	904471
PG 11	M20 x 1.5	25	904472
PG 11	M25 x 1.5	25	904473
PG 13.5	M16 x 1.5	25	904474
PG 13.5	M20 x 1.5	25	904475
PG 13.5	M25 x 1.5	25	904476
PG 16	M20 x 1.5	25	904477
PG 16	M25 x 1.5	25	904478
PG 16	M32 x 1.5	25	904479
PG 21	M25 x 1.5	10	904480
PG 21	M32 x 1.5	10	904481
PG 21	M40 x 1.5	10	904482
PG 29	M40 x 1.5	10	904483
PG 36	M63 x 1.5	10	904486
PG 42	M50 x 1.5	5	904487
PG 42	M63 x 1.5	5	904488