

CV Compact straight



TECHNICAL DATA

Straight-brass nickel- plated conduit gland

Temperature range -45°C to +105°C
Protection class IP 67

■ STRUCTURE

- Material: Brass nickel plated
- O-ring: Nitrile butadiene rubber (NBR)
- Grounding sleeve: steel
- Sealing ring: Polyamide (PA)

■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction

■ NOTES

- Suitable for metallic protection tubes:
 Anaconda Sealtite®:
 EF, HTDL, OR, HC, HCX, ZHLS, HFX

metric thread

Part no.	Size	Weight in kg/1000 pc.	Suitable for tube ND	Suitable for tube outer Ø mm	Spanner size mm	Thread length mm	Packaging unit (in pc.)
908473	M16 x 1.5	3.9	3/8	12.6	24	10.0	10
908474	M20 x 1.5	4.0	3/8	12.6	24	10.0	10
908475	M20 x 1.5	4.4	1/2	16.1	27	10.0	10
908476	M25 x 1.5	6.6	3/4	21.1	33	10.0	5
908477	M32 x 1.5	11.7	1	26.8	42	12.0	5
908478	M40 x 1.5	16.0	1 1/4	35.4	50	13.0	2
908479	M50 x 1.5	25.3	1 1/2	40.3	58	14.0	2
908480	M63 x 1.5	38.6	2	51.6	72	16.0	2