



TECHNICAL DATA

Straight-galvanized steel conduit gland

Temperature range	-45°C to +105°C
Protection class	IP 67

■ STRUCTURE

- Material: steel galvanized

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction
- For Anaconda Sealtite® CNP.
- LIQUIDTIGHT gland made of galvanized steel for plastic-coated metallic protection tubes CNP.

■ APPLICATION

■ NOTES

- The ferrule and insert are from PA 6

NPT thread

Part no.	Size	Suitable for tube ND	Suitable for tube outer Ø mm	Thread length mm	Spanner size mm	Packaging unit (in pc.)
904907	NPT 1/2"	3/8	19.4	15.0	26	25
904908	NPT 1/2"	1/2	23.4	15.0	29	25
904909	NPT 3/4"	3/4	29.5	15.0	35	25
904910	NPT 1"	1	36.3	18.0	42	5
904911	NPT 1 1/4"	1 1/4	46.0	18.0	56	5
904912	NPT 1 1/2"	1 1/2	52.4	18.0	64	1
904913	NPT 2"	2	66.6	18.0	77	1