

HELUTOOL HAP 60-2



TECHNICAL DATA

Battery-powered hydraulic tool in toolbox

■ APPLICATION

- For processing Cable lugs and Connectors up to 300mm²
- Quick infeed due to double piston hydraulic system
- Variable speed for placing the tool
- Ergonomic design for fatigue-free work
- Easy to service and compact design
- Two-piece component handles with optimal weight distribution
- Powerful Li-Ion battery 18 V
- LED to illumination of the workspace
- Crimping area: 6-300 mm²
- Press capacity: approx. 60 kN
- Head rotation: 340°
- Opening range: 17 mm
- Battery voltage: 18 V
- Weight incl. battery: approx. 4,4 kg
- Tool dimensions: 334 x 331 x 75 mm

■ NOTES

- Exclusive inserts
Matching inserts:
HELU-S-PE-SK and HELU-S-PE-WM
Further inserts on request

Scope of delivery:
Battery- powered hydraulic tool
Battery
Battery charger
Carry strap
Manual
Transport case

| Part no. | Type | Packaging unit (in pc.) |
|----------|----------|-------------------------|
| 908494 | HAP 60-2 | 1 |