

HELUTOOL D20



TECHNICAL DATA

Cable Cutter

■ APPLICATION

- VDE approved, 1000V
For cutting copper and aluminium cables, single and multi-core
Low handforce required due to favourable lever ratio and special blade geometry
Clean and smooth cut without crushing and deformation
Initial and final cut (upper and lower blade)
Allows cables of up to 20 mm dia. to be cut
With guard
Handles plastic coated
Precision ground, hardened blades
Adjustable bolted joint, self-retaining screw
High-grade special tool steel, forged, oil-hardened
Weight 340 g

Part no.	Type	Length mm	Packaging unit (in pc.)
904933	HELUTOOL D20	200.0	1

Part no.	Type	Length mm	Packaging unit (in pc.)
----------	------	-----------	-------------------------