

# LT-CNP-E



## TECHNICAL DATA

Straight-stainless steel- conduit gland

Temperature range -45°C to +105°C  
Protection class IP 67

## STRUCTURE

- Material: Stainless steel

## APPLICATION

- Machine and plant construction
  - Robotics
  - Automation technology
  - Vehicle construction and shipbuilding
  - Railway technology
  - Installation technology
  - Control cabinet construction
  - For Anaconda Sealite® CNP.
- LIQUIDTIGHT gland made of stainless steel for plastic-coated metallic protection tubes CNP.

## NOTES

- The ferrule and insert are from PA6.

### metric thread

| Part no. | Size       | Suitable for tube ND | Suitable for tube outer Ø mm | Thread length mm | Spanner size mm | Packaging unit (in pc.) |
|----------|------------|----------------------|------------------------------|------------------|-----------------|-------------------------|
| 905913   | M16 x 1.50 | 3/8                  | 19.4                         | 13.0             | 30              | 10                      |
| 905914   | M20 x 1.50 | 1/2                  | 23.4                         | 13.0             | 36              | 10                      |
| 905058   | M25 x 1.50 | 3/4                  | 29.5                         | 15.0             | 41              | 5                       |
| 905059   | M32 x 1.50 | 1                    | 36.3                         | 15.0             | 50              | 5                       |
| 905060   | M40 x 1.50 | 1 1/4                | 46.0                         | 16.0             | 60              | 2                       |
| 905061   | M50 x 1.50 | 1 1/2                | 52.4                         | 19.0             | 66              | 1                       |
| 905062   | M63 x 1.50 | 1 1/2                | 52.4                         | 19.0             | 81              | 1                       |
| 905063   | M63 x 1.50 | 2                    | 66.6                         | 19.0             | 81              | 1                       |