

CMP



TECHNICAL DATA

Polyolefin shrink tube 2:1

Temperature range -55°C to +135°C

■ STRUCTURE

- Material: Polyolefin

■ PROPERTIES

- silicone-free
- cadmium-free
- lead-free

■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction
- for repairing insulation
- for sealing electrical components

■ NOTES

- Form of shipment:
CMP box (1.2m sections) (25 sections = 30.5m; 10 sections = 12.2m)
CMP rolls

Box

Type	Inner Ø before shrinkage mm	Wandstärke nach Schrumpfung in mm	Inner Ø after shrinkage mm	Packaging unit (in m)	black Part no.
CMP 46-0-A	1.2	0.4	0.6	30.5	91290
CMP 63-0-A	1.6	0.4	0.8	30.5	91291
CMP 125-0-A	3.2	0.5	1.6	30.5	91293
CMP 187-0-A	4.8	0.5	2.4	30.5	91294
CMP 93-0-A	2.4	0.5	1.2	30.5	91292
CMP 250-0-A	6.4	0.6	3.2	30.5	91295
CMP 375-0-A	9.5	0.6	4.8	30.5	91296
CMP 500-0-A	12.7	0.6	6.4	30.5	91297
CMP 750-0-A	19.0	0.8	9.5	12.2	91298
CMP 1000-0-A	25.4	0.9	12.7	12.2	91299