

# PVC-IB



## TECHNICAL DATA

PVC insulating tube acc. to DIN 40621

Temperature range -20°C to +85°C  
short term up to +90°C

## ■ STRUCTURE

- Material: Polyvinyl chloride (PVC)

## ■ PROPERTIES

- silicone-free
- cadmium-free
- self-extinguishing
- weather-resistant
- lead-free

## ■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Installation technology
- Control cabinet construction
- for retrospective insulating
- bundling wires and lines

Inner Ø mm	Wall thickness mm	Packaging unit (in m)	black Part no.
1.0	0.3	200	<b>91310</b>
2.0	0.4	200	<b>91311</b>
3.0	0.4	200	<b>91312</b>
3.5	0.4	200	<b>905179</b>
4.0	0.5	200	<b>91313</b>
4.5	0.5	200	<b>905180</b>
5.0	0.6	200	<b>91314</b>
6.0	0.6	200	<b>91315</b>
7.0	0.7	100	<b>91316</b>
8.0	0.7	100	<b>91317</b>
9.0	0.7	100	<b>91318</b>
10.0	0.7	100	<b>91319</b>
12.0	0.8	100	<b>91320</b>
14.0	1.0	100	<b>97228</b>
16.0	1.0	100	<b>96795</b>
18.0	1.0	50	<b>97281</b>
20.0	1.2	25	<b>97162</b>
22.1	1.2	25	<b>97282</b>
26.0	1.0	25	<b>97283</b>