



TECHNICAL DATA

Crimp cable lug

Flange shape

Fork shape

Temperature range

-60°C to +105°C

■ STRUCTURE

- Material: copper
- Surface: galvanic tin plated
- Insulation: Polyamide (PA)
- partially insulated

■ PROPERTIES

- halogen-free
- widened shaft; allows easy and safe insertion of conductor

■ APPLICATION

- PA insulated solderless terminals for cross sections of 0.25 to 6.0mm².
Simple cable inlet through Easy-Entry (expanded sleeve).
Insulated with high dielectric strength.

■ NOTES

- Legend:
Dimensions
a - Diameter of stud hole
b - Width of flange
d - Inner diameter of wire receptable
L - Length

Pin shape

Part no.	Type	Colour	Cross-sec. mm ² , approx.	ø Stud hole (a) in mm	Packaging unit (in pc.)
91418	HZP	yellow	0.10 - 0.50		100
91419	HAP	red	0.50 - 1.50		100
91420	HBP	blue	1.50 - 2.50		100
91421	HCP	yellow	4.00 - 6.00		100
96575	HDP	red	10.00		100
96576	HEP	blue	16.00		100

Fork shape

Part no.	Type	Colour	Cross-sec. mm ² , approx.	ø Stud hole (a) in mm	Packaging unit (in pc.)
91403	HA 35F	red	0.50 - 1.50	3.7	100
91404	HA 4F	red	0.50 - 1.50	4.3	100
91405	HA 5F	red	0.50 - 1.50	5.3	100
91406	HA 6F	red	0.50 - 1.50	6.5	100
91408	HB 3F	blue	1.50 - 2.50	3.2	100
91409	HB 35F	blue	1.50 - 2.50	3.7	100
91410	HB 4F	blue	1.50 - 2.50	4.3	100
91411	HB 5F	blue	1.50 - 2.50	5.3	100
91412	HB 6F	blue	1.50 - 2.50	6.5	100

Continued on next page

ST-PS / FS



Part no.	Type	Colour	Cross-sec. mm², approx.	ø Stud hole (a) in mm	Packaging unit (in pc.)
91415	HC 4F	yellow	4.00 - 6.00	4.3	100
91416	HC 5F	yellow	4.00 - 6.00	5.3	100
91417	HC 6F	yellow	4.00 - 6.00	6.5	100