


HELU-S-PK-AL/CU



TECHNICAL DATA

Compression cable lug

Flange shape	Ring shape
Connecting angle	180° (horizontal)

■ STRUCTURE

- Material: Aluminium 99,5; Cu acc. to DIN EN 13601
- Surface: bare
- uninsulated
- without Inspection hole

■ APPLICATION

- Non-insulated, straight compression lug in eye type design made of aluminium. High quality version for reliable crimping. Designed for conductor type RM and circular reshaped conductors.

■ NOTES

- Code type indicates the required hexagonal crimping insert. Al-sleeves are prefilled with contact grease and sealed with plastic plugs
- Recommended pressing method: Hexagonal pressing
- Legend:
Dimensions
a - Diameter of stud hole
b - Width of flange
d - Inner diameter of wire receptable
l - Length to centre of hole

Part no.	Cross-sec. mm ²	Stud hole (M)	∅ Stud hole (a) in mm	Flange width (b) in mm	∅ Wire receptable (d) in mm	Length (l) in mm	Code type	Weight in kg/1000 pc.	Packaging unit (in pc.)
907568	10.00	8	8.4	20.0	5.0	50.0	10	26.5	25
907569	16.00 - 25.00	8	8.4	20.0	5.6	60.0	12	35.4	25
907570	16.00 - 25.00	10	10.5	20.0	5.6	60.0	12	34.2	25
907571	25.00 - 35.00	8	8.4	20.0	6.8	65.0	12	35.7	25
907572	25.00 - 35.00	10	10.5	20.0	6.8	65.0	12	34.4	25
907573	25.00 - 35.00	12	13.0	26.0	6.8	67.0	12	44.5	25
907574	35.00 - 50.00	8	8.4	20.0	8.0	75.0	14	45.5	25
907575	35.00 - 50.00	10	10.5	20.0	8.0	75.0	14	44.2	25
907576	35.00 - 50.00	12	13.0	26.0	8.0	75.0	14	51.5	25
907577	50.00 - 70.00	8	8.4	20.0	9.8	75.0	16	48.7	25
907578	50.00 - 70.00	10	10.5	20.0	9.8	75.0	16	47.2	25
907579	50.00 - 70.00	12	13.0	26.0	9.8	75.0	16	59.5	25
907580	70.00 - 95.00	8	8.4	26.0	11.2	85.0	18	61.9	10
907581	70.00 - 95.00	10	10.5	26.0	11.2	85.0	18	73.7	10
907582	70.00 - 95.00	12	13.0	26.0	11.2	85.0	18	71.2	10
907583	70.00 - 95.00	16	17.0	30.0	11.2	88.0	18	81.0	10
907584	95.00 - 120.00	8	8.4	26.0	13.2	86.0	22	102.9	10
907585	95.00 - 120.00	10	10.5	26.0	13.2	86.0	22	105.9	10
907586	95.00 - 120.00	12	13.0	26.0	13.2	86.0	22	103.4	10
907587	95.00 - 120.00	16	17.0	30.0	13.2	88.0	22	109.9	10
907588	120.00 - 150.00	8	8.4	26.0	14.7	88.0	22	106.8	10
907589	120.00 - 150.00	10	10.5	26.0	14.7	88.0	22	106.8	10
907590	120.00 - 150.00	12	13.0	26.0	14.7	88.0	22	104.5	10
907591	120.00 - 150.00	16	17.0	30.0	14.7	90.0	22	114.5	10
907592	150.00 - 185.00	8	8.4	30.0	16.3	100.0	25	138.8	5
906478	150.00 - 185.00	10	10.5	30.0	16.3	100.0	25	138.0	5

Continued on next page

HELU-S-PK-AL/CU

Part no.	Cross-sec. mm ²	Stud hole (M)	∅ Stud hole (a) in mm	Flange width (b) in mm	∅ Wire receptable (d) in mm	Length (l) in mm	Code type	Weight in kg/1000 pc.	Packaging unit (in pc.)
906172	150.00 - 185.00	12	13.0	30.0	16.3	100.0	25	135.7	5
906173	150.00 - 185.00	16	17.0	30.0	16.3	100.0	25	128.8	5
907593	185.00 - 240.00	8	8.4	30.0	18.3	102.0	28	183.7	5
906479	185.00 - 240.00	10	10.5	30.0	18.3	102.0	28	176.1	5
906480	185.00 - 240.00	12	13.0	30.0	18.3	102.0	28	182.1	5
906481	185.00 - 240.00	16	17.0	36.0	18.3	105.0	28	196.8	5
906482	185.00 - 240.00	20	21.0	36.0	18.3	105.0	28	189.7	5
906483	240.00 - 300.00	10	10.5	30.0	21.0	112.0	32	204.1	5
906185	240.00 - 300.00	12	13.0	30.0	21.0	112.0	32	204.1	5
906484	240.00 - 300.00	16	17.0	36.0	21.0	115.0	32	225.8	5
906485	240.00 - 300.00	20	21.0	36.0	21.0	115.0	32	218.5	5
906486	300.00	10	10.5	30.0	23.3	115.0	34	218.4	5
906487	300.00	12	13.0	30.0	23.3	120.5	34	283.3	5
906488	300.00	16	17.0	36.0	23.3	116.0	34	232.2	5
906489	300.00	20	21.0	36.0	23.3	116.0	34	225.0	5
906490	400.00	10	10.5	36.0	26.0	125.0	38	328.7	5
906212	400.00	12	13.0	36.0	26.0	125.0	38	332.8	5
906174	400.00	16	17.0	36.0	26.0	125.0	38	352.6	5
906175	400.00	20	21.0	36.0	26.0	125.0	38	341.5	5
906491	500.00	10	10.5	44.0	29.0	140.0	44	437.1	1
906492	500.00	12	13.0	44.0	29.0	143.0	44	586.2	1
906493	500.00	16	17.0	44.0	29.0	143.0	44	579.8	1
906494	500.00	20	21.0	44.0	29.0	140.0	44	420.8	1
907594	625.00	12	13.0	50.0	35.0	177.0	52	630.1	1
907595	625.00	16	17.0	50.0	35.0	177.0	52	770.0	1
907596	625.00	20	21.0	50.0	35.0	177.0	52	763.0	1