


B-ET



TECHNICAL DATA

Crimp cable lug acc. to DIN 46234

Flange shape Ring shape
Temperature range up to +120°C

■ STRUCTURE

- Material: copper
- Surface: galvanic tin plated
- uninsulated
- without Inspection hole

■ APPLICATION

- Non-insulated solderless terminals in eye type design.

■ NOTES

- Legend:
Dimensions
a - Diameter of stud hole
b - Width of flange
d - Inner diameter of wire receptable
l - Length to centre of hole

Part no.	Type	Cross-sec. mm ²	ø Stud hole (a) in mm	Flange width (b) in mm	ø Wire receptable (d) in mm	Length (l) in mm	Thickness mm	Weight in kg/1000 pc.	Packaging unit (in pc.)
91514	B 1-3	0.50 - 1.50	3.2	6.0	1.6	11.0	1	0.7	100
91515	B 1-4	0.50 - 1.50	4.3	8.0	1.6	12.0	1	0.8	100
91516	B 1-5	0.50 - 1.50	5.3	10.0	1.6	13.0	1	0.8	100
91517	B 2.5-3	1.50 - 2.50	3.2	6.0	2.3	11.0	1	0.6	100
91518	B 2.5-4	1.50 - 2.50	4.3	8.0	2.3	12.0	1	0.8	100
91519	B 2.5-5	1.50 - 2.50	5.3	10.0	2.3	14.0	1	0.9	100
91520	B 2.5-6	1.50 - 2.50	6.5	11.0	2.3	16.0	1	1.1	100
91521	B 6-4	4.00 - 6.00	4.3	8.0	3.6	14.0	1	1.4	100
91522	B 6-5	4.00 - 6.00	5.3	10.0	3.6	15.0	1	1.5	100
91523	B 6-6	4.00 - 6.00	6.5	11.0	3.6	16.0	1	1.6	100
91524	B 6-8	4.00 - 6.00	8.4	14.0	3.6	19.0	1	2.1	100
91525	B 10-5	10.00	5.3	10.0	4.5	16.0	1.1	2.3	100
91526	B 10-6	10.00	6.5	11.0	4.5	17.0	1.1	2.4	100
91527	B 10-8	10.00	8.4	14.0	4.5	20.0	1.1	2.9	100
91528	B 16-5	16.00	5.3	11.0	5.8	20.0	1.2	3.9	100
91529	B 16-6	16.00	6.5	11.0	5.8	20.0	1.2	3.8	100
91530	B 16-8	16.00	8.4	14.0	5.8	22.0	1.2	4.2	100
91531	B 16-10	16.00	10.5	18.0	5.8	24.0	1.2	4.9	100
91532	B 25-6	25.00	6.5	12.0	7.5	25.0	1.5	7.1	50
91533	B 25-8	25.00	8.4	16.0	7.5	25.0	1.5	7.6	50
91534	B 25-10	25.00	10.5	18.0	7.5	26.0	1.5	7.4	50
91535	B 35-8	35.00	8.4	16.0	9.0	26.0	1.6	9.7	50
91536	B 35-10	35.00	10.5	18.0	9.0	27.0	1.6	9.9	50
91537	B 35-12	35.00	13.0	22.0	9.0	31.0	1.6	11.0	50
91538	B 50-8	50.00	8.4	18.0	11.0	34.0	1.8	7.9	50
91539	B 50-10	50.00	10.5	18.0	11.0	34.0	1.8	16.7	50
91540	B 50-12	50.00	13.0	22.0	11.0	36.0	1.8	17.7	50
91541	B 70-10	70.00	10.5	22.0	13.0	38.0	2	25.2	25

B-ET

Part no.	Type	Cross-sec. mm²	ø Stud hole (a) in mm	Flange width (b) in mm	ø Wire receptable (d) in mm	Length (l) in mm	Thickness mm	Weight in kg/1000 pc.	Packaging unit (in pc.)
91542	B 70-12	70.00	13.0	22.0	13.0	38.0	2	21.8	25
91543	B 70-16	70.00	17.0	28.0	13.0	42.0	2	25.6	25
91544	B 95-10	95.00	10.5	24.0	15.0	42.0	2.5	40.0	25
91545	B 95-12	95.00	13.0	24.0	15.0	42.0	2.5	35.7	25
91546	B 95-16	95.00	17.0	28.0	15.0	44.0	2.5	40.0	25
97765	B 120-10	120.00	10.5	24.0	17.0	44.0	3	56.0	25
97766	B 120-12	120.00	13.0	24.0	17.0	44.0	3	54.0	25