


HELU-S-PK-CU



TECHNICAL DATA

Compression cable lug

Flange shape Ring shape
Connecting angle 180° (horizontal)

STRUCTURE

- Material: copper acc. to DIN EN 13600
- Surface: galvanic tin plated
- uninsulated
- without Inspection hole

APPLICATION

- Non-insulated tubular cable lugs in eye type design for conductor arrangement RM.
Tube dimensions to DIN 46235.

NOTES

- Recommended pressing method: Hexagonal pressing
- Legend:
Dimensions
a - Diameter of stud hole
b - Width of flange
d - Inner diameter of wire receptable
l - Length to centre of hole

Part no.	Cross-sec. mm ²	Stud hole (M)	∅ Stud hole (a) in mm	Flange width (b) in mm	∅ Wire receptable (d) in mm	Length (l) in mm	Weight in kg/1000 pc.	Packaging unit (in pc.)
907679	6	8	8.4	13.0	3.7	26.0	3.5	100
907682	10	8	8.4	13.0	4.4	28.0	3.8	100
907683	10	10	10.5	15.0	4.4	29.0	4.0	100
907684	16	5	5.3	13.0	5.5	36.0	12.2	100
907688	16	12	13.0	19.0	5.5	40.0	13.5	100
907693	25	16	17.0	22.0	7.0	45.0	19.9	100
907694	35	6	6.4	17.5	8.2	42.5	31.6	100
907698	35	16	17.0	28.0	8.2	47.0	31.4	100
907699	35	20	21.0	30.0	8.2	53.0	37.3	50
907700	50	6	6.4	20.0	9.8	52.0	46.7	100
907704	50	14	15.0	26.0	9.8	53.5	49.4	100
907706	50	20	21.0	30.0	9.8	61.5	55.6	100
907710	70	14	15.0	24.0	11.3	55.5	60.0	50
907712	70	20	21.0	31.0	11.3	61.0	69.9	50
907713	95	8	8.4	28.0	13.5	65.0	94.4	50
907714	95	14	15.0	28.0	13.5	65.5	94.3	50
907717	120	8	8.4	31.0	15.5	70.0	113.5	50
907718	120	14	15.0	31.0	15.5	70.0	114.1	50
907721	150	8	8.4	34.0	17.0	79.0	164.0	25
907723	150	14	15.0	34.0	17.0	78.0	164.9	25
907725	185	8	8.4	37.0	19.0	83.0	185.0	25
907727	185	14	15.0	37.0	19.0	82.0	189.0	25
907729	240	10	10.5	42.0	21.5	92.0	271.0	20
907730	240	14	15.0	42.5	21.5	92.0	267.3	20
907732	300	10	10.5	48.5	24.5	104.0	348.0	10
907733	300	12	13.0	48.5	24.5	104.0	345.0	10
907734	300	14	15.0	48.5	24.5	104.0	353.6	10

Continued on next page

HELU-S-PK-CU

Part no.	Cross-sec. mm ²	Stud hole (M)	∅ Stud hole (a) in mm	Flange width (b) in mm	∅ Wire receptable (d) in mm	Length (l) in mm	Weight in kg/1000 pc.	Packaging unit (in pc.)
907735	400	10	10.5	55.0	27.5	117.0	734.2	5
907736	400	12	13.0	55.0	27.5	117.0	723.8	5
907737	400	14	15.0	55.0	27.5	117.0	728.4	5
907738	500	12	13.0	60.0	31.0	130.0	869.2	5
907739	500	14	15.0	60.0	31.0	130.0	875.0	5
907740	500	16	17.0	60.0	31.0	130.0	889.0	5
907741	625	12	13.0	63.0	34.5	135.0	842.7	5
907742	625	14	15.0	63.0	34.5	135.0	838.9	5
907743	625	16	17.0	63.0	34.5	135.0	820.5	5
907745	800	14	15.0	75.0	40.0	165.0	1486.0	2
907746	800	16	17.0	75.0	40.0	165.0	1486.0	2
907748	1000	16	17.0	83.0	44.0	167.0	1937.0	2