



TECHNICAL DATA

Threadless PA cable gland acc. to DIN EN 62444

Temperature range	-20°C to +100°C short term -30°C to +150°C
Protection class	IP 66 / IP 68 - 5 bar

STRUCTURE

- Material: Polyamide (PA) 6, V2 acc. to UL 94
- Seal: Chloroprene rubber (CR)
- with patented spring/snap system without tools

PROPERTIES

- optimum strain relief through clamping lamella
- easy to assemble, time and cost savings

- eng nebeneinander montierbar
- watertight, dust-tight
- large clamping areas

APPLICATION

- Installation without the use of special tools. No threaded holes or lock nuts required. Compatibility with the HELUTOP® HT series enables problem-free integration into existing systems. For wall thickness range: 0,5-4,0 mm

NOTES

- Additional colors on request.
- Legend:
Dimensions
TD - Thread Diameter
TL - Thread Length

metric thread

Ø Drill hole mm	Size	Cable Ø from / to mm	Spanner size mm	Packaging unit (in pc.)	grey (RAL 7035)	grey (RAL 7001)	black (RAL 9005)
					Part no.	Part no.	Part no.
16.3	M16	5.0 - 10.0	22	50	908054	908060	908062
20.3	M20	6.0 - 12.0	24	50	908055	908061	-
20.3	M20	6.0 - 12.0	24	25	-	-	908063
25.3	M25	11.0 - 17.0	29	25	908368	908383	908385
32.3	M32	15.0 - 21.0	36	25	908369	908384	-
32.3	M32	15.0 - 21.0	36	50	-	-	908386