



## TECHNICAL DATA

PVC shrink tube 2:1

Temperature range -20°C to +90°C

### ■ STRUCTURE

- Material: Polyvinyl chloride (PVC) V0 acc. to UL 94

### ■ PROPERTIES

- silicone-free

### ■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Installation technology
- Control cabinet construction
- for repairing insulation
- for sealing electrical components

### ■ NOTES

- Attention: Do not store tubes at over 18°C! Otherwise properties are changed!  
Length shrinkage approx. 20-30%  
The colours orange, yellow, white, blue, green, brown, red on request.

Inner Ø before shrinkage mm	Inner Ø after shrinkage mm	Wall thickness mm	Packaging unit (in m)	black Part no.
2.5	1.2	0.45	100	<b>91300</b>
4	2	0.5	100	<b>91301</b>
6	3	0.5	100	<b>91302</b>
7	4	0.5	100	<b>91303</b>
11	6	0.6	100	<b>91304</b>
14	8	0.6	100	<b>91305</b>
17	10	0.8	100	<b>91306</b>
20	13	0.8	100	<b>91307</b>
25	16	1.0	50	<b>91308</b>
31	20	1.0	50	<b>91309</b>