



TECHNICAL DATA

Crimp cable lug

Flange shape Push-on receptacle
Temperature range -25°C to +105°C

■ STRUCTURE

- Material: copper
- Surface: galvanic tin plated
- Insulation: Polyamide (PA)
- partially insulated

■ PROPERTIES

- halogen-free

■ NOTES

- Legend:
 Dimensions
 b - Width of flange
 d - Inner diameter of wire receptacle
 L - Length

Push-on receptacle

Part no.	Type	Colour	Cross-sec. mm ² , approx.	Flat plug size in mm	Design	Packaging unit (in pc.)
91431	RA 28	red	0.50 - 1.00	2.80 x 0.80	Sleeve	100
91432	RA 29	red	0.50 - 1.00	2.80 x 0.50	Sleeve	100
91434	RA 48	red	0.50 - 1.00	4.80 x 0.80	Sleeve	100
91433	RA 49	red	0.50 - 1.00	4.80 x 0.50	Sleeve	100
91435	RA 63	red	0.50 - 1.00	6.30 x 0.80	Sleeve	100
96428	RB 28	blue	1.50 - 2.50	2.80 x 0.80	Sleeve	100
96415	RB 29	blue	1.50 - 2.50	2.80 x 0.50	Sleeve	100
91438	RB 48	blue	1.50 - 2.50	4.80 x 0.80	Sleeve	100
91439	RB 49	blue	1.50 - 2.50	4.80 x 0.50	Sleeve	100
91440	RB 63	blue	1.50 - 2.50	6.30 x 0.80	Sleeve	100
91443	RC 63	yellow	4.00 - 6.00	6.30 x 0.80	Sleeve	100
91445	RC 95	yellow	4.00 - 6.00	9.50 x 1.20	Sleeve	100

Flat-pin plug

Part no.	Type	Colour	Cross-sec. mm ² , approx.	Flat plug size in mm	Design	Packaging unit (in pc.)
98701	RA 28 M	red	0.50 - 1.00	2.80 x 0.80	Plugs	100
98700	RA 29 M	red	0.50 - 1.00	2.80 x 0.50	Plugs	100
98584	RA 48 M	red	0.50 - 1.00	4.80 x 0.80	Plugs	100
98577	RA 49 M	red	0.50 - 1.00	4.80 x 0.50	Plugs	100
91437	RA 63 M	red	0.50 - 1.00	6.30 x 0.80	Plugs	100
98599	RB 48 M	blue	1.50 - 2.50	4.80 x 0.80	Plugs	100
91442	RB 63 M	blue	1.50 - 2.50	6.30 x 0.80	Plugs	100

ST-PR / FP



Part no.	Type	Colour	Cross-sec. mm ² , approx.	Flat plug size in mm	Design	Packaging unit (in pc.)
98598	RB49 M	blue	1.50 - 2.50	4.80 x 0.50	Plugs	100
91444	RC 63 M	yellow	4.00 - 6.00	6.30 x 0.80	Plugs	100