


B-FT



TECHNICAL DATA

Crimp cable lug acc. to DIN 46230

Flange shape Fork shape
Temperature range up to +120°C

■ STRUCTURE

- Material: copper
- Surface: galvanic tin plated
- uninsulated
- without Inspection hole

■ APPLICATION

- Non-insulated solderless terminals in fork design.

■ NOTES

- Legend:
Dimensions
a - Diameter of stud hole
b - Width of flange
d - Inner diameter of wire receptable
l - Length to centre of hole

Part no.	Type	Cross-sec. mm ²	∅ Stud hole (a) in mm	Flange width (b) in mm	∅ Wire receptable (d) in mm	Length (l) in mm	Weight in kg/1000 pc.	Packaging unit (in pc.)
91547	B 1-4F	0.50 - 1.50	4.3	7.0	1.6	12.0	0.7	100
91548	B 1-5F	0.50 - 1.50	5.3	9.6	1.6	13.0	0.9	100
91550	B 2.5-4F	1.50 - 2.50	4.3	7.0	2.3	12.0	0.8	100
91551	B 2.5-5F	1.50 - 2.50	5.3	9.6	2.3	13.0	0.9	100
91552	B 2.5-6F	1.50 - 2.50	6.5	12.0	2.3	13.0	1.1	100
91553	B 6-4F	4.00 - 6.00	4.3	8.5	3.6	14.0	1.4	100
91554	B 6-5F	4.00 - 6.00	5.3	9.0	3.6	14.0	1.6	100
91555	B 6-6F	4.00 - 6.00	6.5	12.5	3.6	18.0	1.7	100