

# HELUcond PA12



## TECHNICAL DATA

### PA Corrugated tubes

Temperature range	-40°C to +120°C short term up to +150°C
Capacity/100mm	approx. 350 N (NW: 17)

### ■ STRUCTURE

- Material: modified Polyamide (PA) 12
- Flammability acc. to UL 94 (HB)

### ■ PROPERTIES

- halogen-free
- cadmium-free

- resistant to: fuels, mineral oils, greases, weak bases, weak acids

### ■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Railway technology
- Installation technology
- Cable protection tube for heavy-duty applications.  
High flexible and high load rating

### ■ NOTES

- Fine or coarse profile. Suitable connection glands: HELUquick, HSSV.

## PA12-F

Nominal size mm	Inner Ø mm	Outer Ø mm, approx.	Packaging unit (in m)	grey	black
				Part no.	Part no.
10.0	9.8	13.0	50	<b>920156</b>	<b>920163</b>
12.0	12.0	15.8	50	<b>920157</b>	<b>920164</b>
17.0	16.6	21.0	50	<b>920158</b>	<b>920165</b>

## PA12-B

Nominal size mm	Inner Ø mm	Outer Ø mm, approx.	Packaging unit (in m)	grey	black
				Part no.	Part no.
21.0	22.0	28.5	50	<b>920159</b>	<b>920166</b>
29.0	27.5	34.5	25	<b>920160</b>	<b>920167</b>
36.0	35.2	42.5	25	<b>920161</b>	<b>920168</b>
48.0	46.5	54.5	25	<b>920162</b>	<b>905796</b>