



TECHNICAL DATA

Corrugated tubes conduit gland

Temperature range -40°C to +110°C

Protection class IP 65

STRUCTURE

- Material: Polyamide (PA) 6
- Flammability acc. to UL 94 (V0)

PROPERTIES

- halogen-free
- cadmium-free
- resistant to: fuels, mineral oils, greases, weak bases, weak acids

APPLICATION

- Machine and plant construction
 - Robotics
 - Automation technology
 - Vehicle construction and shipbuilding
 - Railway technology
 - Installation technology
 - Control cabinet construction
 - Quick-insert glands with metallic female thread for a reliable, quick connection.
- Suitable for parallel-coiled HELUcond protection tubes.

- NOTES**
- Protection classification: IP 66 with outer seal
 - Threaded connection: metric to EN 60423
 - Each unit includes 1 safety opener

metric thread – female

Size	Suitable for nominal size	Thread length mm	Spanner size mm	Packaging unit (in pc.)	grey	black
					Part no.	Part no.
M12 x 1.5	10	8.0	19	50	920273	920281
M16 x 1.5	10	10.0	19	50	920274	920282
M16 x 1.5	12	10.0	21	50	920275	920283
M20 x 1.5	16 / 17	13.0	27	50	920276	920284
M25 x 1.5	21 / 23	13.5	36	50	920277	920285
M32 x 1.5	29	14.0	40	25	920278	920286
M40 x 1.5	36 / 37	15.0	50	25	920279	920287
M50 x 1.5	48 / 50	16.0	65	10	920280	920288

08.04.2024 / We reserve the right to make technical changes; the imprint in the image is purely exemplary