



BHA / BHB / BHC forked



TECHNICAL DATA

Crimp cable lug acc. to DIN EN 45545-2

Flange shape	Fork shape
Temperature range	-20°C to +115°C short term up to +130°C

■ STRUCTURE

- Material: Brass
- Surface: galvanic tin plated
- Insulation: Polycarbonat (PC)
- partially insulated
- Flammability acc. to UL 94 (V0)

■ APPLICATION

- Polycarbonate-insulated connection material on tape has been developed as a cost-effective solution for medium and large pre-fabricated cables.

■ NOTES

- Roll diameter: 450mm
Inner diameter of inclusion: 27mm
Blade terminal / blade receptacle / pin-type cable lug on tape on request.
- Legend:
a - Diameter of stud hole
b - Width of flange
d - Inner diameter of wire receptacle
l - Length to centre of hole

Part no.	Type	Colour	Cross-sec. mm ² , approx.	Packaging unit (in pc.)
93754	BHA 35 F	red	0.25 - 1.50	2000
93755	BHA 4 F	red	0.25 - 1.50	2000
93756	BHA 5 F	red	0.25 - 1.50	2000
93757	BHA 6 F	red	0.25 - 1.50	2000
93758	BHB 3 F	blue	1.50 - 2.50	1750
93759	BHB 35 F	blue	1.50 - 2.50	1750

Part no.	Type	Colour	Cross-sec. mm ² , approx.	Packaging unit (in pc.)
93760	BHB 4 F	blue	1.50 - 2.50	1750
93761	BHB 5 F	blue	1.50 - 2.50	1750
93762	BHB 6 F	blue	1.50 - 2.50	1750
93763	BHC 4 F	yellow	4.00 - 6.00	1250
93764	BHC 5 F	yellow	4.00 - 6.00	1250
93765	BHC 6 F	yellow	4.00 - 6.00	1250