


EW round

Transition from small to large thread



TECHNICAL DATA

Nickel plated brass extender

Temperature range up to +200°C

■ STRUCTURE

- Material: Brass, nickel plated

■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction

■ NOTES

- Legend:
Dimensions
TD - Thread Diameter
SI - Size of the internal thread
TL - Thread Length
D - Outer diameter

from metric to metric

Part no.	Size outside	Size inside	Thread length mm	Outer Ø mm, approx.	Packaging unit (in pc.)
94064	M12 x 1.5	M16 x 1.5	5.0	18.0	100
94066	M16 x 1.5	M20 x 1.5	5.0	22.0	100
94069	M20 x 1.5	M25 x 1.5	6.0	27.0	50
94072	M25 x 1.5	M32 x 1.5	7.0	34.0	50

Part no.	Size outside	Size inside	Thread length mm	Outer Ø mm, approx.	Packaging unit (in pc.)
94075	M32 x 1.5	M40 x 1.5	8.0	42.0	50
94078	M40 x 1.5	M50 x 1.5	8.0	52.0	25
94081	M50 x 1.5	M63 x 1.5	9.0	66.0	10

from PG to PG

Part no.	Size outside	Size inside	Thread length mm	Outer Ø mm, approx.	Packaging unit (in pc.)
90630	PG 7	PG 9	5.0	17.0	100
90631	PG 9	PG 11	6.0	20.0	100
90632	PG 9	PG 13.5	6.0	22.0	100
90633	PG 11	PG 13.5	6.0	22.0	100
90634	PG 11	PG 16	6.0	24.0	100
90635	PG 13.5	PG 16	6.5	24.0	100

Part no.	Size outside	Size inside	Thread length mm	Outer Ø mm, approx.	Packaging unit (in pc.)
90636	PG 13.5	PG 21	6.5	30.0	50
90637	PG 16	PG 21	6.5	30.0	50
90638	PG 21	PG 29	7.0	39.0	50
90639	PG 29	PG 36	8.0	50.0	25
90640	PG 36	PG 42	9.0	57.0	25
90641	PG 42	PG 48	10.0	64.0	10