


HELU-S-PV-CU-DIN



TECHNICAL DATA

Copper compression joint acc. to EN 13600 E-Cu joint

■ STRUCTURE

- Material: copper
- Surface: tinned

■ APPLICATION

- Clamping connection sleeves for unstrained clamping of conductors built to DIN 46267.

■ NOTES

- Code type indicates the required hexagonal clamping insert
- Legend:
Dimensions
d - Inner diameter
L - Length

Part no.	Type	Cross-sec. mm ² , approx.	Inner Ø mm	Length mm	Code type	Weight in kg/1000 pc.	Packaging unit (in pc.)
93263	HELU-S-PV-CU-DIN 6	6	3.8	30.0	5.5	3.4	50
93264	HELU-S-PV-CU-DIN 10	10	4.5	30.0	6	3.4	50
93265	HELU-S-PV-CU-DIN 16	16	5.5	50.0	8.5	14.9	50
93266	HELU-S-PV-CU-DIN 25	25	7.0	50.0	10	18.0	50
93267	HELU-S-PV-CU-DIN 35	35	8.2	50.0	12.5	31.5	50
93268	HELU-S-PV-CU-DIN 50	50	10.0	56.0	14.5	43.7	50
93269	HELU-S-PV-CU-DIN 70	70	11.5	56.0	16.5	55.4	25
93270	HELU-S-PV-CU-DIN 95	95	13.5	70.0	19	88.4	25
93271	HELU-S-PV-CU-DIN 120	120	15.5	70.0	21	99.2	25
93272	HELU-S-PV-CU-DIN 150	150	17.0	80.0	23.5	148.6	10
93273	HELU-S-PV-CU-DIN 185	185	19.0	85.0	25.5	173.5	10
93274	HELU-S-PV-CU-DIN 240	240	21.5	90.0	29	240.3	10
93275	HELU-S-PV-CU-DIN 300	300	24.5	100.0	32	298.6	10