


# RE round

## Transition from large to small thread



### TECHNICAL DATA

Nickel plated round brass reducer

Temperature range up to +200°C

### ■ STRUCTURE

- Material: Brass, nickel plated

### ■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Installation technology
- Control cabinet construction

### ■ NOTES

- Legend:  
Dimensions  
TD - Thread Diameter  
SI - Size of the internal thread

#### from metric to metric

Part no.	Size outside	Size inside	Thread length mm	Outer Ø mm, approx.	Packaging unit (in pc.)
94065	M16 x 1.5	M12 x 1.5	5.0	18.0	100
94067	M20 x 1.5	M12 x 1.5	6.0	22.0	100
94068	M20 x 1.5	M16 x 1.5	6.0	22.0	100
94070	M25 x 1.5	M16 x 1.5	7.0	27.0	50
904407	M25 x 1.5	M20 x 1.5	7.0	27.0	100
904408	M32 x 1.5	M20 x 1.5	8.0	34.0	25
94074	M32 x 1.5	M25 x 1.5	8.0	34.0	50

Part no.	Size outside	Size inside	Thread length mm	Outer Ø mm, approx.	Packaging unit (in pc.)
904409	M40 x 1.5	M25 x 1.5	8.0	43.0	25
94077	M40 x 1.5	M32 x 1.5	8.0	43.0	25
94079	M50 x 1.5	M32 x 1.5	9.0	53.0	10
94080	M50 x 1.5	M40 x 1.5	9.0	53.0	25
94082	M63 x 1.5	M40 x 1.5	10.0	66.0	10
94083	M63 x 1.5	M50 x 1.5	10.0	66.0	10

#### from PG to PG

Part no.	Size outside	Size inside	Thread length mm	Outer Ø mm, approx.	Packaging unit (in pc.)
904410	PG 9	PG 7	6.0	17.0	100
904411	PG 11	PG 7	6.0	20.0	100
904412	PG 11	PG 9	6.0	20.0	100
904413	PG 13.5	PG 9	6.5	22.0	100
904415	PG 16	PG 13.5	6.5	24.0	100
904414	PG 16	PG 7	6.5	24.0	100

Part no.	Size outside	Size inside	Thread length mm	Outer Ø mm, approx.	Packaging unit (in pc.)
904416	PG 21	PG 13.5	7.0	30.0	50
904417	PG 21	PG 16	7.0	30.0	50
904418	PG 29	PG 16	8.0	39.0	25
904419	PG 29	PG 21	8.0	39.0	50
904420	PG 42	PG 29	10.0	57.0	25