


PE-WN

closed



TECHNICAL DATA

PE hex head blanking plug

Temperature range	-30°C to +100°C
Protection class	IP 54

■ STRUCTURE

- Material: Polyethylene (PE)
- with flexible plastic lead-through diaphragm for simple cable inlet

■ PROPERTIES

- halogen-free

■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction

■ NOTES

- Open Hex head blanking plug: on request.
- Legend:
TD - Thread Diameter
TL - Thread Length

metric thread

Size	Cable Ø from / to mm	Thread length mm	Packaging unit (in pc.)	grey (RAL 7035) Part no.
M12 x 1.5	3.0 - 5.0	10.0	100	94120
M16 x 1.5	5.0 - 10.0	10.0	100	94121
M20 x 1.5	8.0 - 13.5	12.0	100	94122
M25 x 1.5	9.0 - 16.0	12.0	100	94123
M32 x 1.5	11.0 - 22.0	14.0	50	94124
M40 x 1.5	17.0 - 24.0	16.0	25	94125
M50 x 1.5	22.0 - 35.0	18.0	5	94126
M63 x 1.5	24.0 - 43.0	20.0	5	94127

PG thread

Size	Cable Ø from / to mm	Thread length mm	Packaging unit (in pc.)	grey (RAL 7035) Part no.
PG 9	6.0 - 8.0	12.0	100	90116
PG 11	7.0 - 10.0	14.0	100	90117
PG 13.5	9.0 - 12.0	17.0	100	90118
PG 16	9.0 - 14.0	19.0	100	90119
PG 21	11.0 - 17.0	24.0	50	90120

Continued on next page

PE-WN



closed

Size	Cable Ø from / to mm	Thread length mm	Packaging unit (in pc.)	grey (RAL 7035) Part no.
PG 29	17.0 - 24.0	13.0	25	90121
PG 36	25.0 - 32.0	12.0	15	90122