

# Adapter PA

for thread adjustment from metric to PG



## TECHNICAL DATA

PA adapter

Temperature range -40°C to +100°C

## ■ STRUCTURE

- Material: Polyamide (PA)

## ■ PROPERTIES

- halogen-free
- phosphor-free
- silicone-free

## ■ APPLICATION

- Machine and plant construction
- Automation technology
- Vehicle construction and shipbuilding
- Installation technology
- Control cabinet construction

## ■ NOTES

- Black on request.
- Legend:  
Dimensions  
TD - Thread Diameter  
SI - Size of the internal thread

## from metric to PG

Size outside	Size inside	Packaging unit (in pc.)	grey (RAL 7035) Part no.
M12 x 1.5	PG 7	100	<b>93670</b>
M12 x 1.5	PG 9	100	<b>93671</b>
M16 x 1.5	PG 9	100	<b>93672</b>
M20 x 1.5	PG 11	100	<b>93673</b>
M20 x 1.5	PG 13.5	100	<b>93674</b>
M20 x 1.5	PG 16	100	<b>93675</b>
M25 x 1.5	PG 16	50	<b>93676</b>
M25 x 1.5	PG 21	50	<b>93677</b>
M32 x 1.5	PG 29	25	<b>93678</b>
M40 x 1.5	PG 29	10	<b>93679</b>
M50 x 1.5	PG 36	10	<b>93680</b>
M50 x 1.5	PG 42	10	<b>93681</b>
M63 x 1.5	PG 48	10	<b>93682</b>

# Adapter PA

## for thread adjustment from metric to PG

### from PG to metric

Size outside	Size inside	Packaging unit (in pc.)	grey (RAL 7035) Part no.
PG 11	M16 x 1.5	100	<b>93655</b>
PG 11	M20 x 1.5	100	<b>93656</b>
PG 13.5	M16 x 1.5	100	<b>93657</b>
PG 13.5	M20 x 1.5	100	<b>93658</b>
PG 13.5	M25 x 1.5	100	<b>93659</b>
PG 16	M20 x 1.5	100	<b>93660</b>
PG 16	M25 x 1.5	50	<b>93661</b>
PG 21	M25 x 1.5	50	<b>93662</b>
PG 21	M32 x 1.5	50	<b>93663</b>
PG 29	M32 x 1.5	50	<b>93664</b>
PG 29	M40 x 1.5	50	<b>93665</b>
PG 7	M12 x 1.5	100	<b>93650</b>
PG 7	M16 x 1.5	100	<b>93651</b>
PG 9	M12 x 1.5	100	<b>93652</b>
PG 9	M16 x 1.5	100	<b>93653</b>
PG 9	M20 x 1.5	100	<b>93654</b>